


NOTES: UNLESS OTHERWISE SPECIFIED

1. P/N: X100WCOLOR
HOUSING & PLUNGER: MOLDED NYLON TYPE 6,6.
AVAILABLE IN TEN COLORS.
CONTACT BLADE: BERYLLIUM COPPER PER QQ-C-533. GOLD PLATED PER MIL-G-45204 B TYPE 1 0.00001 [0.000254] THICK MINIMUM.
SPRING: STAINLESS STEEL TYPE 302.
2. P/N: 9260COLOR
HOUSING: MOLDED NYLON. AVAILABLE IN TEN COLORS.
FRAME: BRASS. NICKEL PLATED
CONTACT: BeCu OR PHOSPHOR BRONZE. NICKEL PLATED.
3. P/N: W-600/COLOR
18AWG 65X36 TINNED COPPER
0.144 [3.66] O.D. PVC INSULATION
AVAILABLE IN TEN COLORS.
4. PERFORMANCE
MAXIMUM CURRENT: 4.0 AMPS
MAXIMUM VOLTAGE: 5000 W.V.D.C.
MAXIMUM TEMPERATURE: 221°F (105°C)



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES		CONTRACT NO.		DESCRIPTION	
		± .XX ± .XXX ±		APPROVALS	DATE	EZ-HOOK DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A. MINI-HOOK (X100W) TO STK BANANA PLUG (9260)	
				DRAWN			
				APPROVED BY	9/10		
		MATERIAL SEE NOTE.				SIZE CODE IDENT NO. DRAWING NO.	
		FINISH SEE NOTE.				A 08505 601W	
		NEXT ASSY USED ON				SCALE 1:1	
		APPLICATION DO NOT SCALE DRAWING				SHEET 1 OF 1	