


Knurled Head Thumb Screws

561-T0440018, 561-T0440025, 561-T0440037, 561-T0440050, 561-T0440075, 561-T0632025, 561-T0632037, 561-T0632050, 561-T0632075, 561-T0632100, 561-T0832018, 561-T0832037, 561-T0832050, 561-T0832075, 561-T0832100, 561-T1032050, 561-T1032075, 561-T1032100, 561-T1032150, 561-T1032200, 561-T2520050, 561-T2520075, 561-T2520100, 561-T2520125, 561-T2520150

Last Revised: 06/29/10



Dimensions: in.

Item Number	Description	Thread Size	A	B	C	Length
561-T0440018	440 X 0.187	440	0.300(± .010)	0.280(± .010)	0.125(± 0.005)	0.187(± 0.000/0.020)
561-T0440025	440 X 0.25	440	0.300(± .010)	0.280(± .010)	0.125(± 0.005)	0.250(± 0.000/0.020)
561-T0440037	440 X 0.375	440	0.300(± .010)	0.280(± .010)	0.125(± 0.005)	0.375(± 0.000/0.020)
561-T0440050	440 X 0.5	440	0.300(± .010)	0.280(± .010)	0.125(± 0.005)	0.500(± 0.000/0.020)
561-T0440075	440 X 0.75	440	0.300(± .010)	0.280(± .010)	0.125(± 0.005)	0.750(± 0.000/0.020)
561-T0632025	632 X 0.25	632	0.360(± .010)	0.275(± .010)	0.125(± 0.005)	0.250(± 0.000/0.020)
561-T0632037	632 X 0.375	632	0.360(± .010)	0.275(± .010)	0.125(± 0.005)	0.375(± 0.000/0.020)
561-T0632050	632 X 0.5	632	0.360(± .010)	0.275(± .010)	0.125(± 0.005)	0.500(± 0.000/0.020)
561-T0632075	632 X 0.75	632	0.360(± .010)	0.275(± .010)	0.125(± 0.005)	0.750(± 0.000/0.030)
561-T0632100	632 X 1	632	0.360(± .010)	0.275(± .010)	0.125(± 0.005)	1.000(± 0.000/0.030)
561-T0832018	832 X 0.187	832	0.425(± .010)	0.305(± .010)	0.140(± 0.005)	0.187(± 0.000/0.020)
561-T0832037	832 X 0.375	832	0.425(± .010)	0.305(± .010)	0.140(± 0.005)	0.375(± 0.000/0.020)
561-T0832050	832 X 0.5	832	0.425(± .010)	0.305(± .010)	0.140(± 0.005)	0.500(± 0.000/0.020)
561-T0832075	832 X 0.75	832	0.425(± .010)	0.305(± .010)	0.140(± 0.005)	0.750(± 0.000/0.030)
561-T0832100	832 X 1	832	0.425(± .010)	0.305(± .010)	0.140(± 0.005)	1.000(± 0.000/0.030)
561-T1032050	1032 X 0.5	1032	0.425(± .010)	0.325(± .010)	0.140(± 0.005)	0.750(± 0.000/0.020)
561-T1032075	1032 X 0.75	1032	0.425(± .010)	0.325(± .010)	0.140(± 0.005)	0.187(± 0.000/0.030)
561-T1032100	1032 X 1	1032	0.425(± .010)	0.325(± .010)	0.140(± 0.005)	1.000(± 0.000/0.030)
561-T1032150	1032 X 1.5	1032	0.425(± .010)	0.325(± .010)	0.140(± 0.005)	1.500(± 0.000/0.060)
561-T1032200	1032 X 2	1032	0.425(± .010)	0.325(± .010)	0.140(± 0.005)	2.000(± 0.000/0.060)
561-T2520050	1/4-20 X 0.5	1/4-20	0.540(± .010)	0.365(± .010)	0.155(± 0.005)	0.005(± 0.000/0.030)
561-T2520075	1/4-20 X 0.75	1/4-20	0.540(± .010)	0.365(± .010)	0.155(± 0.005)	0.750(± 0.000/0.030)
561-T2520100	1/4-20 X 1	1/4-20	0.540(± .010)	0.365(± .010)	0.155(± 0.005)	1.000(± 0.000/0.030)
561-T2520125	1/4-20 X 1.25	1/4-20	0.540(± .010)	0.365(± .010)	0.155(± 0.005)	1.250(± 0.000/0.060)
561-T2520150	1/4-20 X 1.5	1/4-20	0.540(± .010)	0.365(± .010)	0.155(± 0.005)	1.500(± 0.000/0.060)

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

EPD-200887

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eagle Plastic Devices:

[561-T0832018](#) [561-T0832050](#) [561-T0440025](#) [561-T0440037](#) [561-T0440075](#) [561-T2520150](#) [561-T2520125](#) [561-T2520100](#) [561-T0632025](#) [561-T0440018](#) [561-T0440050](#) [561-T0632075](#) [561-T0632037](#) [561-T0632050](#) [561-T1032100](#) [561-T2520050](#) [561-T0832100](#) [561-T2520075](#) [561-T0832075](#) [561-T0832037](#) [561-T0632100](#) [561-T1032200](#) [561-T1032050](#) [561-T1032075](#)