

Pelican M6 2320

www.pelicanproducts.us



M6 2320 Flashlight

The M6 2320 Flashlight uses 2 CR123 lithium cells (included) to power a hi-pressure Xenon lamp for intense brightness. The tough CNC-machined aluminum chassis has a knurled body for a secure grip. Plus, the convenient push button tail cap switch has a safety lockout feature to prevent inadvertent battery depletion or accidental activation. It comes with a free Cordura® holster with back-up battery pouch. The M6 2320 is the ideal tactical flashlight, with its durable design and blinding beam.

CAUTION: This Pelican Flashlight is a high output Professional Grade Lighting Product and can generate significant heat and light intensity. Do not leave activated flashlight unattended. Do not cover activated flashlight. Do not place activated flashlight against combustible material or material that could be damaged by heat. Keep activated flashlight well ventilated. If the lamp is activated while in a case or other container, the lamp could overheat and cause damage to surrounding materials.

Minimum Pack 6 ea.

Packaged Weight: 9.5 oz.

M6 2320 Flashlight Specifications

High		
LIGHT SOURCE	Xenon	
BATTERIES	2 CR123 Lithium (Included)	
CHARGE TIME	N/A	
VOLTAGE	6	
LENGTH	5.51" (14 cm)	
WEIGHT w/ BATTERIES	5.6 oz. (0.16 kg)	
WEIGHT w/o BATTERIES	4.4 oz. (0.12 kg)	

FL1 STANDARD		
LIGHT OUTPUT	82 LUMENS	
RUNTIME (hours/min)	1h 15m	
BEAM DISTANCE (meters)	145m	
PEAK BEAM INTENSITY (candela)	5260cd	

M6 2320 Flashlight Configurations

Cat. #	Description
2320	M6 2320 Flashlight (Carded)

NSN List

NSN #	Description
6230-01-503-8719	2320B Black
6240-01-503-8717	2324 Lamp Module

M6 2320 Flashlight Accessories

Cat. #	Description
610	Front Sight Mount
620	Side Sling Mount
630	Foregrip Mount
770	Universal Helmet Light Holder
2324	M6 Xenon Lamp
2326	Remote Pressure Switch
2327	Cordura® Holster
23220R	Traffic Wand (Orange)
2322YW	Traffic Wand (Yellow)
2325BLUE	M6 Blue Filter Cap
2325IR	M6 IR Filter Cap
2325RED	M6 Red Filter Cap