

001

FILE NO.

BB-CD-805-02


- ① MAT'L: COPPER (STOCK TKN. .031)
PLATING: ELECTRO TIN (.0003 MIN)
- ② TIN-PLATED BRASS FUNNEL FERRULE
- ③ NYLON INSULATION (COLOR CODED BLUE)

STUD SIZES: (+.005)

02 = .094
04 = .119
06 = .146
08 = .173
10 = .198
14 = .265
56 = .328
38 = .390

"UL" LISTING #E32244
"CSA" LISTING #18689

WIRE SIZE: 16 - 14 AWG
1.0 - 2.5 MM²



ALL DIMENSIONS = $\frac{\text{INCHES}}{\text{MM}}$ (MWID) = DENOTES MAXIMUM WIRE INSULATION DIAMETER

PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.	"D" ±.005	AVAILABLE STUD SIZES	TITLE:	
						SCALE: NTS	DATE
BB-8707	$\frac{.250}{6.35}$	$\frac{.230}{5.84}$	$\frac{.825}{20.96}$	$\frac{1.05}{2.67}$	05 ($\frac{.127 \pm .005}{3.23}$)		
BB-8707-	$\frac{.250}{6.35}$	$\frac{.230}{5.84}$	$\frac{.825}{20.96}$	$\frac{1.14}{2.90}$	06		
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED						DWG. NO. A CUSTOMER DWG	
FRAC.	DEC.	ANG.	REFERENCE	SCALE: NTS	DATE	TITLE: SNAP SPADE SHORT TONGUE TERMINAL AVIKRIMP 800-SERIES	
±	±	±		DRWN. BY: JJ	11-9-84		
				CHKD. BY: GZ	11-29-84		
				APPRD. BY:			