

RF Cable Assembly Guide



Electrical Ratings

Electrical ratings of a cable assembly are determined by the limiting connector type and cable size.

Connector	Cable	Connector Frequency Impedance (Ohms)	GHz	Dielectric Withstanding Voltage (Vms)	Working Voltage (Vms)
MMCX	RG-178	50 Ohms	6 GHz	500 Vms	170 Vms
	RG-316	50 Ohms	6 GHz	500 Vms	170 Vms
MCX	RG-178	50 Ohms	6 GHz	750 Vms	250 Vms
	RG-316	50 Ohms	6 GHz	1000 Vms	335 Vms
	RG-316 DS	50 Ohms	6 GHz	1000 Vms	335 Vms
MCX 75 Ohm	RG-179	75 Ohms	6 GHz	1000 Vms	335 Vms
	BELDEN 735A	75 Ohms	6 GHz	1000 Vms	335 Vms
SMA	RG-178	50 Ohms	12.4 GHz	500 Vms	170 Vms
	RG-316	50 Ohms	12.4 GHz	750 Vms	250 Vms
	RG-316 DS	50 Ohms	12.4 GHz	750 Vms	250 Vms
	RG-58	50 Ohms	12.4 GHz	1000 Vms	335 Vms
	RG-142	50 Ohms	12.4 GHz	1000 Vms	335 Vms
	Hand Formable .086	50 Ohms	26.5 GHz	1000 Vms	335 Vms
	Hand Formable .141	50 Ohms	26.5 GHz	1500 Vms	500 Vms
SMB	RG-178	50 Ohms	4 GHz	750 Vms	250 Vms
	RG-316	50 Ohms	4 GHz	1000 Vms	335 Vms
SMB Mini 75 Ohm	RG-179	75 Ohms	2 GHz	1000 Vms	335 Vms
	RG-179 DS	75 Ohms	2 GHz	1000 Vms	335 Vms
	BELDEN 735A	75 Ohms	2 GHz	1000 Vms	335 Vms
BNC	RG-58	50 Ohms	4 GHz	1500 Vms	500 Vms
	BELDEN 8218	50 Ohms	4 GHz	1500 Vms	500 Vms
	RG-59	50 Ohms	4 GHz	1500 Vms	500 Vms
	RG-59 PLENUM	50 Ohms	4 GHz	1500 Vms	500 Vms
BNC True 75 Ohm	BELDEN 8218	75 Ohms	3 GHz	1500 Vms	500 Vms
	RG-59	75 Ohms	3 GHz	1500 Vms	500 Vms
	BELDEN 8281	75 Ohms	3 GHz	1500 Vms	500 Vms
	COMM SCOPE 735	75 Ohms	3 GHz	1500 Vms	500 Vms
	BELDEN 735A	75 Ohms	3 GHz	1500 Vms	500 Vms
	BELDEN 734A	75 Ohms	3 GHz	1500 Vms	500 Vms
	BELDEN 1694A	75 Ohms	3 GHz	1500 Vms	500 Vms
N Type	RG-58	50 Ohms	11 GHz	1500 Vms	500 Vms
	RG-142	50 Ohms	11 GHz	1500 Vms	500 Vms
	RG-8	50 Ohms	11 GHz	1500 Vms	500 Vms
	RG-213	50 Ohms	11 GHz	1500 Vms	500 Vms

Cable Length Tolerance


Standard Cable Length	Cable Tolerance	Metric Cable Length	Cable Tolerance
≤1 ft	+1 in - 0.25 in	≤0.3 m	+25 mm - 6 mm
>1 ft - 5 ft	+2 in - 1 in	>0.3 m - 1.5 m	+50 mm - 25 mm
>5 ft - 10 ft	+4 in - 2 in	>1.5 m - 3 m	+100 mm - 50 mm
>10 ft - 25 ft	+6 in - 3 in	>3 m - 7.5 m	+150 mm - 75 mm
>25 ft	+2 % - 1 %	>7.5 m	+2 % - 1 %

Custom Solutions

Johnson offers more than 500 standard fixed length cable assemblies, with various connector configurations and lengths. Johnson also has more than 400 custom cable assemblies, which were designed to meet customer design specification requirements. If you do not see the cable assembly you require, we can design and manufacture one to meet your unique specifications.

- Available Cable Options:
Flexible, Semi-Rigid and Conformable
 - CNC Hardline Bender (Semi-Rigid Cables)
- Available Connector Options:
Standard and Custom
 - Voltage/Continuity Tested
- 0 to 40 GHz
 - 50 and 75 Ohms
 - Prototype available upon request

Measurements of Cable Length



Johnson’s cable length applies to the end of straight connectors. The length is applied to the vertical centroid of right angle connectors.

Part Number Index

4

1

5

Connector Type

-

Connector Type

-

Standard Cable Length

Part Number Example: 415-0037-012

Part Number Description: 12" length cable

4

1

5

Connector Type

-

Connector Type

-

M

M

Metric Cable Connector Length
(less than 1 m)

Part Number Example: 415-0037-MM150

Part Number Description: 150 mm length cable

4

1

5

Connector Type

-

Connector Type

-

M

.

Metric Cable Connector Length
(1 m and greater)

Part Number Example: 415-0037-M1.5

Part Number Description: 1.5 m length cable

MMCX Straight Plug to MMCX Straight Plug

Connector by Cable Type: **RG-178** (135-3402-001) **RG-316** (135-3403-001)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0066-006	6"	152 mm	RG-178	415-0067-006	6"	152 mm	RG-316
415-0066-012	12"	305 mm	RG-178	415-0067-012	12"	305 mm	RG-316
415-0066-018	18"	457 mm	RG-178	415-0067-018	18"	457 mm	RG-316
415-0066-024	24"	610 mm	RG-178	415-0067-024	24"	610 mm	RG-316

MMCX Right Angle Plug to MMCX Right Angle Plug

Connector by Cable Type: **RG-178** (135-3402-101) **RG-316** (135-3403-101)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0068-MM150	5.9"	150 mm	RG-178	415-0069-MM150	5.9"	150 mm	RG-316
415-0068-006	6"	152 mm	RG-178	415-0069-006	6"	152 mm	RG-316
415-0068-MM250	9.84"	250 mm	RG-178	415-0069-MM250	9.84"	250 mm	RG-316
415-0068-012	12"	305 mm	RG-178	415-0069-012	12"	305 mm	RG-316
415-0068-018	18"	457 mm	RG-178	415-0069-018	18"	457 mm	RG-316
415-0068-MM500	19.7"	500 mm	RG-178	415-0069-MM500	19.7"	500 mm	RG-316
415-0068-024	24"	610 mm	RG-178	415-0069-024	24"	610 mm	RG-316
415-0068-MM750	29.53"	750 mm	RG-178	415-0069-MM750	29.53"	750 mm	RG-316

MMCX Straight Plug to SMA Straight Bulkhead Jack

Connector by Cable Type: **RG-178** (135-3402-001, 142-0302-431) **RG-316** (135-3403-001, 142-0303-411)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0070-MM150	5.9"	150 mm	RG-178	415-0071-MM150	5.9"	150 mm	RG-316
415-0070-006	6"	152 mm	RG-178	415-0071-006	6"	152 mm	RG-316
415-0070-MM250	9.84"	250 mm	RG-178	415-0071-MM250	9.84"	250 mm	RG-316
415-0070-012	12"	305 mm	RG-178	415-0071-012	12"	305 mm	RG-316
415-0070-018	18"	457 mm	RG-178	415-0071-018	18"	457 mm	RG-316
415-0070-MM500	19.7"	500 mm	RG-178	415-0071-MM500	19.7"	500 mm	RG-316
415-0070-024	24"	610 mm	RG-178	415-0071-024	24"	610 mm	RG-316
415-0070-MM750	29.53"	750 mm	RG-178	415-0071-MM750	29.53"	750mm	RG-316
415-0070-036	36"	914 mm	RG-178	415-0071-036	36"	914 mm	RG-316
415-0070-M1.0	39.4"	1000 mm	RG-178	415-0071-M1.0	39.4"	1000 mm	RG-316

MMCX Right Angle Plug to SMA Straight Bulkhead Jack

Connector by Cable Type: **RG-178** (135-3402-101, 142-0302-431) **RG-316** (135-3403-101, 142-0303-411)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0072-006	6"	152 mm	RG-178	415-0073-MM150	5.9"	150 mm	RG-316
415-0072-012	12"	305 mm	RG-178	415-0073-006	6"	152 mm	RG-316
415-0072-018	18"	457 mm	RG-178	415-0073-MM250	9.84"	250 mm	RG-316
415-0072-024	24"	610 mm	RG-178	415-0073-012	12"	305 mm	RG-316
415-0072-036	36"	914 mm	RG-178	415-0073-018	18"	457 mm	RG-316
				415-0073-MM500	19.7"	500 mm	RG-316
				415-0073-024	24"	610 mm	RG-316
				415-0073-MM750	29.53"	750mm	RG-316
				415-0073-036	36"	914 mm	RG-316
				415-0073-M1.0	39.4"	1000 mm	RG-316

MCX Straight Plug to MCX Straight Plug

Connector by Cable Type: **RG-178** (133-3402-021) **RG-316** (133-3403-001) **RG-316 DS** (133-3404-001)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0014-006	6"	152 mm	RG-178	415-0018-024	24"	610 mm	RG-316
415-0014-012	12"	305 mm	RG-178	415-0018-030	30"	762 mm	RG-316
415-0014-018	18"	457 mm	RG-178	415-0018-036	36"	914 mm	RG-316
415-0014-024	24"	610 mm	RG-178	415-0020-006	6"	152 mm	RG-316 DS
415-0014-030	30"	762 mm	RG-178	415-0020-012	12"	305 mm	RG-316 DS
415-0014-036	36"	914 mm	RG-178	415-0020-018	18"	457 mm	RG-316 DS
415-0018-006	6"	152 mm	RG-316	415-0020-024	24"	610 mm	RG-316 DS
415-0018-012	12"	305 mm	RG-316	415-0020-030	30"	762 mm	RG-316 DS
415-0018-018	18"	457 mm	RG-316	415-0020-036	36"	914 mm	RG-316 DS

MCX Straight Plug to MCX Straight Bulkhead Jack

Connector by Cable Type: **RG-316** (133-3403-001, 133-3303-401)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0016-MM150	5.9"	150 mm	RG-316	415-0016-MM500	19.7"	500 mm	RG-316
415-0016-006	6"	152 mm	RG-316	415-0016-024	24"	610 mm	RG-316
415-0016-MM250	9.84"	250 mm	RG-316	415-0016-MM750	29.53"	750 mm	RG-316
415-0016-012	12"	305 mm	RG-316	415-0016-030	30"	762 mm	RG-316
415-0016-018	18"	457 mm	RG-316	415-0016-036	36"	914 mm	RG-316
				415-0016-M1.0	39.4"	1000 mm	RG-316

MCX Straight Plug to MCX Right Angle Plug

Connector by Cable Type: **RG-316** (133-3403-001, 133-3403-101)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0017-006	6"	152 mm	RG-316	415-0017-024	24"	610 mm	RG-316
415-0017-012	12"	305 mm	RG-316	415-0017-030	30"	762 mm	RG-316
415-0017-018	18"	457 mm	RG-316	415-0017-036	36"	914 mm	RG-316

MCX Right Angle Plug to MCX Right Angle Plug

Connector by Cable Type: **RG-178** (133-3402-101) **RG-316** (133-3403-101) **RG-316 DS** (133-3404-101)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0015-MM150	5.9"	150 mm	RG-178	415-0019-MM250	9.84"	250 mm	RG-316
415-0015-006	6"	152 mm	RG-178	415-0019-012	12"	305 mm	RG-316
415-0015-MM250	9.84"	250 mm	RG-178	415-0019-024	24"	610 mm	RG-316
415-0015-012	12"	305 mm	RG-178	415-0019-MM750	29.53"	750 mm	RG-316
415-0015-018	18"	457 mm	RG-178	415-0019-036	36"	914 mm	RG-316
415-0015-MM500	19.7"	500 mm	RG-178	415-0019-M1.0	39.4"	1000 mm	RG-316
415-0015-024	24"	610 mm	RG-178	415-0021-006	6"	152 mm	RG-316 DS
415-0015-MM750	29.53"	750 mm	RG-178	415-0021-012	12"	305 mm	RG-316 DS
415-0015-036	36"	914 mm	RG-178	415-0021-018	18"	457 mm	RG-316 DS
415-0015-M1.0	39.4"	1000 mm	RG-178	415-0021-024	24"	610 mm	RG-316 DS
415-0019-MM150	5.9"	150 mm	RG-316	415-0021-036	36"	914 mm	RG-316 DS
415-0019-006	6"	152 mm	RG-316				

MCX 75 Ohm Straight Plug to MCX 75 Ohm Straight Plug

Connector by Cable Type: **RG-179** (133-8433-001) **Belden 735A** (133-8445-001)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0022-006	6"	152 mm	RG-179	415-0023-006	6"	152 mm	Belden 735A
415-0022-012	12"	305 mm	RG-179	415-0023-012	12"	305 mm	Belden 735A
415-0022-018	18"	457 mm	RG-179	415-0023-018	18"	457 mm	Belden 735A
415-0022-024	24"	610 mm	RG-179	415-0023-024	24"	610 mm	Belden 735A
415-0022-030	30"	762 mm	RG-179	415-0023-030	30"	762 mm	Belden 735A
415-0022-036	36"	914 mm	RG-179	415-0023-036	36"	914 mm	Belden 735A

MCX 75 Ohm Right Angle Plug to MCX 75 Ohm Right Angle Plug

Connector by Cable Type: **Belden 735A** (133-8445-101)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0024-006	6"	152 mm	Belden 735A	415-0024-024	24"	610 mm	Belden 735A
415-0024-012	12"	305 mm	Belden 735A	415-0024-030	30"	762 mm	Belden 735A
415-0024-018	18"	457 mm	Belden 735A	415-0024-036	36"	914 mm	Belden 735A

SMA Straight Plug to SMA Straight Plug

Connector by Cable Type: **RG-178** (142-0402-011) **RG-316** (142-0403-011) **RG-316 DS** (142-0404-011) **RG-58** (142-0407-011) **RG-142** (142-0408-011)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0025-MM150	5.9"	150 mm	RG-178	415-0033-012	12"	305 mm	RG-316 DS
415-0025-006	6"	152 mm	RG-178	415-0033-018	18"	457 mm	RG-316 DS
415-0025-MM250	9.84"	250 mm	RG-178	415-0033-MM500	19.7"	500 mm	RG-316 DS
415-0025-012	12"	305 mm	RG-178	415-0033-024	24"	610 mm	RG-316 DS
415-0025-018	18"	457 mm	RG-178	415-0033-MM750	29.53"	750 mm	RG-316 DS
415-0025-MM500	19.7"	500 mm	RG-178	415-0033-036	36"	914 mm	RG-316 DS
415-0025-024	24"	610 mm	RG-178	415-0033-048	48"	1219 mm	RG-316 DS
415-0025-MM750	29.53"	750 mm	RG-178	415-0033-M1.0	39.4"	1000 mm	RG-316 DS
415-0025-036	36"	914 mm	RG-178	415-0033-M1.5	59.1"	1500 mm	RG-316 DS
415-0025-048	48"	1219 mm	RG-178	415-0033-M2.0	78.7"	2000 mm	RG-316 DS
415-0025-M1.0	39.4"	1000 mm	RG-178	415-0038-MM250	9.84"	250 mm	RG-58
415-0025-M1.5	59.1"	1500 mm	RG-178	415-0038-012	12"	305 mm	RG-58
415-0029-MM150	5.9"	150 mm	RG-316	415-0038-MM500	19.7	500 mm	RG-58
415-0029-006	6"	152 mm	RG-316	415-0038-024	24"	610 mm	RG-58
415-0029-MM250	9.84"	250 mm	RG-316	415-0038-036	24"	762 mm	RG-58
415-0029-012	12"	305 mm	RG-316	415-0038-048	36"	914 mm	RG-58
415-0029-018	18"	457 mm	RG-316	415-0038-M1.0	39.4"	1000 mm	RG-58
415-0029-MM500	19.7"	500 mm	RG-316	415-0038-M1.5	59.1"	1500 mm	RG-58
415-0029-024	24"	610 mm	RG-316	415-0038-060	60"	1524 mm	RG-58
415-0029-MM750	29.53"	750 mm	RG-316	415-0038-M2.0	78.7"	2000 mm	RG-58
415-0029-036	36"	914 mm	RG-316	415-0043-MM250	9.84"	250 mm	RG-142
415-0029-048	48"	1219 mm	RG-316	415-0043-012	12"	305 mm	RG-142
415-0029-M1.0	39.4"	1000 mm	RG-316	415-0043-MM500	19.7	500 mm	RG-142
415-0029-M1.5	59.1"	1500 mm	RG-316	415-0043-024	24"	610 mm	RG-142
415-0029-M2.0	78.7"	2000 mm	RG-316	415-0043-036	36"	914 mm	RG-142
415-0029-M3.0	118.1"	3000 mm	RG-316	415-0043-M1.0	39.4"	1000 mm	RG-142
415-0033-MM150	5.9"	150 mm	RG-316 DS	415-0043-048	48"	1219 mm	RG-142
415-0033-006	6"	152 mm	RG-316 DS	415-0043-M1.5	59.1"	1500 mm	RG-142
415-0033-MM250	9.84"	250 mm	RG-316 DS	415-0043-060	60"	1524 mm	RG-142

SMA Straight Hand Formable Plug to SMA Straight Hand Formable Plug

Connector by Cable Type: **0.086 Conformable** (142-0693-001)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0081-MM75	2.95"	75 mm	.086
415-0081-003	3"	76 mm	.086
415-0081-MM100	3.93"	100 mm	.086
415-0081-004	4"	102 mm	.086
415-0081-MM125	4.9"	125 mm	.086
415-0081-005	5"	127 mm	.086
415-0081-MM150	5.9"	150 mm	.086
415-0081-006	6"	152 mm	.086
415-0081-MM175	6.89"	175 mm	.086

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0081-007	7"	178 mm	.086
415-0081-MM200	7.87"	200 mm	.086
415-0081-008	8"	203 mm	.086
415-0081-MM250	9.84"	250 mm	.086
415-0081-012	12"	305 mm	.086
415-0081-018	18"	457 mm	.086
415-0081-MM500	19.7"	500 mm	.086
415-0081-024	24"	610 mm	.086
415-0081-MM750	29.53"	750 mm	.086

SMA Straight Hand Formable Plug to SMA Straight Hand Formable Plug

Connector by Cable Type: **0.141 Conformable** (142-0694-001)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0082-MM75	2.95"	75 mm	.141
415-0082-003	3"	76 mm	.141
415-0082-MM100	3.93"	100 mm	.141
415-0082-004	4"	102 mm	.141
415-0082-MM125	4.9"	125 mm	.141
415-0082-005	5"	127 mm	.141
415-0082-MM150	5.9"	150 mm	.141
415-0082-006	6"	152 mm	.141
415-0082-MM175	6.89"	175 mm	.141

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0082-007	7"	178 mm	.141
415-0082-MM200	7.87"	200 mm	.141
415-0082-008	8"	203 mm	.141
415-0082-MM250	9.84"	250 mm	.141
415-0082-012	12"	305 mm	.141
415-0082-018	18"	457 mm	.141
415-0082-MM500	19.7"	500 mm	.141
415-0082-024	24"	610 mm	.141
415-0082-MM750	29.53"	750 mm	.141

SMA Straight Plug to SMA Straight Bulkhead Jack

Connector by Cable Type: **RG-316** (142-0403-011, 142-0303-411) **RG-316 DS** (142-0404-011, 142-0304-411) **RG-58** (142-0407-011, 142-0307-411) **RG-142** (142-0408-011, 142-0308-411)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0031-MM150	5.9"	150 mm	RG-316
415-0031-006	6"	152 mm	RG-316
415-0031-MM250	9.84"	250 mm	RG-316
415-0031-012	12"	305 mm	RG-316
415-0031-018	18"	457 mm	RG-316
415-0031-MM500	19.7"	500 mm	RG-316
415-0031-024	24"	610 mm	RG-316
415-0031-MM750	29.53"	750 mm	RG-316
415-0031-036	36"	914 mm	RG-316
415-0031-M1.0	39.4"	1000 mm	RG-316
415-0031-048	48"	1219 mm	RG-316
415-0031-M1.5	59.1"	1500 mm	RG-316
415-0035-006	6"	152 mm	RG-316 DS
415-0035-012	12"	305 mm	RG-316 DS

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0035-018	18"	457 mm	RG-316 DS
415-0035-024	24"	610 mm	RG-316 DS
415-0035-036	36"	914mm	RG-316 DS
415-0035-048	48"	1219mm	RG-316 DS
415-0040-012	12"	305 mm	RG-58
415-0040-024	24"	610 mm	RG-58
415-0040-036	36"	914 mm	RG-58
415-0040-048	48"	1219 mm	RG-58
415-0040-060	60"	1524 mm	RG-58
415-0045-012	12"	305 mm	RG-142
415-0045-024	24"	610 mm	RG-142
415-0045-036	36"	914mm	RG-142
415-0045-048	48"	1219 mm	RG-142
415-0045-060	60"	1524 mm	RG-142

SMA Straight Plug to SMA Right Angle Plug

Connector by Cable Type: **RG-178** (142-0402-011, 142-0402-101) **RG-316** (142-0403-011, 142-0403-101) **RG-316 DS** (142-0404-011, 142-0404-101) **RG-142** (142-0408-011, 142-0408-101)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0026-006	6"	152 mm	RG-178
415-0026-012	12"	305 mm	RG-178
415-0026-018	18"	457 mm	RG-178
415-0026-024	24"	610 mm	RG-178
415-0026-036	36"	914mm	RG-178
415-0026-048	48"	152 mm	RG-178
415-0030-MM150	5.9"	150 mm	RG-316
415-0030-006	6"	152 mm	RG-316
415-0030-MM250	9.84"	250 mm	RG-316
415-0030-012	12"	305 mm	RG-316
415-0030-018	18"	457 mm	RG-316
415-0030-MM500	19.7"	500 mm	RG-316
415-0030-024	24"	610 mm	RG-316
415-0030-MM750	29.53"	750 mm	RG-316
415-0030-036	36"	914 mm	RG-316
415-0030-M1.0	39.4"	1000 mm	RG-316
415-0030-048	48"	1219 mm	RG-316
415-0030-M1.5	59.1"	1500 mm	RG-316

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0034-MM150	5.9"	150 mm	RG-316 DS
415-0034-006	6"	152 mm	RG-316 DS
415-0034-MM250	9.84"	250 mm	RG-316 DS
415-0034-012	12"	305 mm	RG-316 DS
415-0034-018	18"	457 mm	RG-316 DS
415-0034-MM500	19.7"	500 mm	RG-316 DS
415-0034-024	24"	610 mm	RG-316 DS
415-0034-MM750	29.53"	750 mm	RG-316 DS
415-0034-036	36"	914 mm	RG-316 DS
415-0034-M1.0	39.4"	1000 mm	RG-316 DS
415-0034-048	48"	1219 mm	RG-316 DS
415-0034-M1.5	59.1"	1500 mm	RG-316 DS
415-0044-012	12"	305 mm	RG-142
415-0044-024	24"	610 mm	RG-142
415-0044-036	36"	914mm	RG-142
415-0044-048	48"	1219 mm	RG-142
415-0004-060	60"	1524 mm	RG-142

SMA Right Angle Plug to SMA Right Angle Plug

Connector by Cable Type: **RG-178** (142-0402-101) **RG-316** (142-0403-101) **RG-316 DS** (142-0404-101) **RG-58** (142-0407-101) **RG-142** (142-0408-101)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0027-MM150	5.9"	150 mm	RG-178
415-0027-006	6"	152 mm	RG-178
415-0027-MM250	9.84"	250 mm	RG-178
415-0027-012	12"	305 mm	RG-178
415-0027-024	24"	610 mm	RG-178
415-0027-MM750	29.53"	750 mm	RG-178
415-0027-036	36"	914 mm	RG-178
415-0027-M1.0	39.4"	1000 mm	RG-178
415-0027-048	48"	1219 mm	RG-178
415-0027-M1.5	59.1"	1500 mm	RG-178
415-0032-MM150	5.9"	150 mm	RG-316
415-0032-006	6"	152 mm	RG-316
415-0032-MM250	9.84"	250 mm	RG-316
415-0032-012	12"	305 mm	RG-316
415-0032-MM500	19.7"	500 mm	RG-316
415-0032-018	18"	457 mm	RG-316
415-0032-024	24"	610 mm	RG-316
415-0032-MM750	29.53"	750 mm	RG-316
415-0032-036	36"	914 mm	RG-316

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0032-M1.0	39.4"	1000 mm	RG-316
415-0032-048	48"	1219 mm	RG-316
415-0032-M1.5	59.1"	1500 mm	RG-316
415-0036-006	6"	152 mm	RG-316 DS
415-0036-012	12"	305 mm	RG-316 DS
415-0036-018	18"	457 mm	RG-316 DS
415-0036-024	24"	610 mm	RG-316 DS
415-0036-036	36"	914 mm	RG-316 DS
415-0036-048	48"	1219 mm	RG-316 DS
415-0041-012	12"	305 mm	RG-58
415-0041-024	24"	610 mm	RG-58
415-0041-036	36"	914mm	RG-58
415-0041-048	48"	1219 mm	RG-58
415-0041-060	60"	1524 mm	RG-58
415-0046-012	12"	305 mm	RG-142
415-0046-024	24"	610 mm	RG-142
415-0046-036	36"	914mm	RG-142
415-0046-048	48"	1219 mm	RG-142
415-0046-060	60"	1524 mm	RG-142

SMA Right Angle Plug to SMA Straight Bulkhead Jack

Connector by Cable Type: **RG-316** (142-0403-101, 142-0303-411) **RG-316 DS** (142-0404-101, 142-0304-411) **RG-142** (142-0408-101, 142-0308-411)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0074-006	6"	152 mm	RG-316	415-0064-036	36"	914 mm	RG-316 DS
415-0074-012	12"	305 mm	RG-316	415-0064-048	48"	1219 mm	RG-316 DS
415-0074-024	24"	610 mm	RG-316	415-0075-006	6"	152 mm	RG-142
415-0074-036	36"	914 mm	RG-316	415-0075-012	12"	305 mm	RG-142
415-0074-048	48"	1219 mm	RG-316	415-0075-024	24"	610 mm	RG-142
415-0064-006	6"	152 mm	RG-316 DS	415-0075-036	36"	914 mm	RG-142
415-0064-012	12"	305 mm	RG-316 DS	415-0075-048	48"	1219 mm	RG-142
415-0064-024	24"	610 mm	RG-316 DS				

SMA Quick-Connect Straight Plug to SMA Quick-Connect Straight Plug

Connector by Cable Type: **RG-316** (142-1403-001) **RG-316 DS** (142-1404-001) **RG-142** (142-1408-001)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0065-006	6"	152 mm	RG-316	415-0076-012	12"	305 mm	RG-316 DS
415-0065-012	12"	305 mm	RG-316	415-0076-024	24"	610 mm	RG-316 DS
415-0065-018	18"	457 mm	RG-316	415-0076-036	36"	914 mm	RG-316 DS
415-0065-024	24"	610 mm	RG-316	415-0077-012	12"	305 mm	RG-142
415-0065-036	36"	914 mm	RG-316	415-0077-024	24"	610 mm	RG-142
415-0065-048	48"	1219 mm	RG-316	415-0077-036	36"	914 mm	RG-142

SMA Quick-Connect Straight Plug to SMA Straight Plug

Connector by Cable Type: **RG-316 DS** (142-1404-001, 142-0404-011) **RG-142** (142-1408-001, 142-0408-011)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0078-012	12"	305 mm	RG-316 DS	415-0079-012	12"	305 mm	RG-142
415-0078-024	24"	610 mm	RG-316 DS	415-0079-024	24"	610 mm	RG-142
415-0078-036	36"	914 mm	RG-316 DS	415-0079-036	36"	914 mm	RG-142

SMA Straight Bulkhead Jack to Right Angle MCX Plug

Connector by Cable Type: **RG-316 DS** (142-0304-411, 133-3404-101)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0181-006	6"	152 mm	RG-316 DS	415-0181-036	36"	914 mm	RG-316 DS
415-0181-012	12"	305 mm	RG-316 DS	415-0181-048	48"	1219 mm	RG-316 DS
415-0181-024	24"	610 mm	RG-316 DS	415-0181-060	60"	1524 mm	RG-316 DS

SMB Straight Plug to SMB Straight Plug

Connector by Cable Type: **RG-316** (131-1403-001)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0003-MM150	5.9"	150 mm	RG-316
415-0003-006	6"	152 mm	RG-316
415-0003-MM250	9.84"	250 mm	RG-316
415-0003-012	12"	305 mm	RG-316
415-0003-018	18"	457 mm	RG-316

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0003-MM500	19.7"	500 mm	RG-316
415-0003-024	24"	610 mm	RG-316
415-0003-MM750	29.53"	750 mm	RG-316
415-0003-036	36"	914 mm	RG-316
415-0003-M1.0	39.4"	1000 mm	RG-316

SMB Straight Plug to SMB Right Angle Plug

Connector by Cable Type: **RG-178** (131-3402-001, 131-1402-101) **RG-316** (131-1403-001, 131-1403-101) **RG-316 DS** (131-1404-001, 131-1404-101)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0007-006	6"	152 mm	RG-178
415-0007-012	12"	305 mm	RG-178
415-0007-018	18"	457 mm	RG-178
415-0007-024	24"	610 mm	RG-178
415-0007-030	30"	762 mm	RG-178
415-0007-036	36"	914 mm	RG-178
415-0002-006	6"	152 mm	RG-316
415-0002-012	12"	305 mm	RG-316
415-0002-018	18"	457 mm	RG-316

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0002-024	24"	610 mm	RG-316
415-0002-030	30"	762 mm	RG-316
415-0002-036	36"	914 mm	RG-316
415-0005-006	6"	152 mm	RG-316 DS
415-0005-012	12"	305 mm	RG-316 DS
415-0005-018	18"	457 mm	RG-316 DS
415-0005-024	24"	610 mm	RG-316 DS
415-0005-030	30"	762 mm	RG-316 DS
415-0005-036	36"	914 mm	RG-316 DS

SMB Right Angle Plug to SMB Right Angle Plug

Connector by Cable Type: **RG-178** (131-1402-101) **RG-316** (131-1403-101) **RG-316 DS** (131-1404-101)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0001-MM150	5.9"	150 mm	RG-178
415-0001-006	6"	152 mm	RG-178
415-0001-MM250	9.84"	250 mm	RG-178
415-0001-012	12"	305 mm	RG-178
415-0001-018	18"	457 mm	RG-178
415-0001-MM500	19.7"	500 mm	RG-178
415-0001-024	24"	610 mm	RG-178
415-0001-MM750	29.53"	750 mm	RG-178
415-0001-030	30"	762 mm	RG-178
415-0001-036	36"	914 mm	RG-178
415-0001-M1.0	39.4"	1000 mm	RG-178
415-0004-MM150	5.9"	150 mm	RG-316
415-0004-006	6"	152 mm	RG-316
415-0004-MM250	9.84"	250 mm	RG-316

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0004-012	12"	305 mm	RG-316
415-0004-018	18"	457 mm	RG-316
415-0004-MM500	19.7"	500 mm	RG-316
415-0004-024	24"	610 mm	RG-316
415-0004-MM750	29.53"	750 mm	RG-316
415-0004-030	30"	762 mm	RG-316
415-0004-036	36"	914 mm	RG-316
415-0004-M1.0	39.4"	1000 mm	RG-316
415-0006-006	6"	152 mm	RG-316 DS
415-0006-012	12"	305 mm	RG-316 DS
415-0006018	18"	457 mm	RG-316 DS
415-0006-024	24"	610 mm	RG-316 DS
415-0006-030	30"	762 mm	RG-316 DS
415-0006-036	36"	914 mm	RG-316 DS

SMB Mini-75 Ohm Straight Plug to SMB Mini-75 Ohm Straight Plug

Connector by Cable Type: **RG-179** (131-8403-011) **RG-179 DS** (131-8404-011)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0008-006	6"	152 mm	RG-179	415-0010-006	6"	152 mm	RG-179 DS
415-0008-012	12"	305 mm	RG-179	415-0010-012	12"	305 mm	RG-179 DS
415-0008-018	18"	457 mm	RG-179	415-0010-018	18"	457 mm	RG-179 DS
415-0008-024	24"	610 mm	RG-179	415-0010-024	24"	610 mm	RG-179 DS
415-0008-030	30"	762 mm	RG-179	415-0010-030	30"	762 mm	RG-179 DS
415-0008-036	36"	914 mm	RG-179	415-0010-036	36"	914 mm	RG-179 DS

SMB Mini-75 Ohm Right Angle Plug to SMB Mini-75 Ohm Right Angle Plug

Connector by Cable Type: **RG-179** (131-8403-111) **RG-179 DS** (131-8404-111) **Belden 735A** (131-8445-101)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0009-006	6"	152 mm	RG-179	415-0011-024	24"	610 mm	RG-179 DS
415-0009-012	12"	305 mm	RG-179	415-0011-030	30"	762 mm	RG-179 DS
415-0009-018	18"	457 mm	RG-179	415-0011-036	36"	914 mm	RG-179 DS
415-0009-024	24"	610 mm	RG-179	415-0013-006	6"	152 mm	Belden 735A
415-0009-030	30"	762 mm	RG-179	415-0013-012	12"	305 mm	Belden 735A
415-0009-036	36"	914 mm	RG-179	415-0013-018	18"	457 mm	Belden 735A
415-0011-006	6"	152 mm	RG-179 DS	415-0013-024	24"	610 mm	Belden 735A
415-0011-012	12"	305 mm	RG-179 DS	415-0013-030	30"	762 mm	Belden 735A
415-0011-018	18"	457 mm	RG-179 DS	415-0013-036	36"	914 mm	Belden 735A

N Straight Plug to N Straight Plug

Connector by Cable Type: **RG-58** (CPN-1) **RG-142** (CPN-142T) **RG-8** (CPN-8) **RG-213** (CPN-8)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0058-012	12"	305 mm	RG-58	415-0062-012	12"	305 mm	RG-8
415-0058-024	24"	610 mm	RG-58	415-0062-024	24"	610 mm	RG-8
415-0058-036	36"	914 mm	RG-58	415-0062-036	36"	914 mm	RG-8
415-0058-048	48"	1219 mm	RG-58	415-0062-048	48"	1219 mm	RG-8
415-0058-060	60"	1524 mm	RG-58	415-0062-060	60"	1524 mm	RG-8
415-0060-012	12"	305 mm	RG-142	415-0063-012	12"	305 mm	RG-213
415-0060-024	24"	610 mm	RG-142	415-0063-024	24"	610 mm	RG-213
415-0060-036	36"	914 mm	RG-142	415-0063-036	36"	914 mm	RG-213
415-0060-048	48"	1219 mm	RG-142	415-0063-048	48"	1219 mm	RG-213
415-0060-060	60"	1524 mm	RG-142	415-0063-060	60"	1524 mm	RG-213

BNC Straight Plug to BNC Straight Plug with Boot

Connector by Cable Type: **RG-58** (CPMC-88-1) **RG-58 PLENUM** (CPMC-88-10) **RG-59** (CPMC-88-2) **Belden 8218** (CPMC-88-18)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0054-MM250	9.84"	250 mm	RG-58	415-0055-048	48"	1219 mm	RG-59 PLENUM
415-0054-012	12"	305 mm	RG-58	415-0055-060	60"	1524 mm	RG-59 PLENUM
415-0054-MM500	19.7"	500 mm	RG-58	415-0057-012	12"	305 mm	RG-59
415-0054-024	24"	610 mm	RG-58	415-0057-024	24"	610 mm	RG-59
415-0054-MM750	29.53"	750 mm	RG-58	415-0057-036	36"	914 mm	RG-59
415-0054-036	36"	914 mm	RG-58	415-0057-048	48"	1219 mm	RG-59
415-0054-M1.0	39.4"	1000 mm	RG-58	415-0057-060	60"	1524 mm	RG-59
415-0054-048	48"	1219 mm	RG-58	With Heatshrink			
415-0054-M1.5	59.1"	1500 mm	RG-58	415-0056-012	12"	305 mm	Belden 8218
415-0054-060	60"	1524 mm	RG-58	415-0056-024	24"	610 mm	Belden 8218
415-0055-012	12"	305 mm	RG-59 PLENUM	415-0056-036	36"	914 mm	Belden 8218
415-0055-024	24"	610 mm	RG-59 PLENUM	415-0056-048	48"	1219 mm	Belden 8218
415-0055-036	36"	914 mm	RG-59 PLENUM	415-0056-060	60"	1524 mm	Belden 8218

75 Ohm BNC Straight Plug to 75 Ohm BNC Straight Plug with Boot or Heatshrink

Connector by Cable Type: **RG-59** (CPMC-68-2) **Belden 734A** (CPMC-68-35) **Belden 8218** (CPMC-68-18) **Belden 8281** (CPMC-68-3) **Commscope 735** (CPMC-68-33) **Belden 735A** (CPMC-68-33) **Belden 1694A** (CPMC-68-45)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type	Part Number	Standard Cable Length	Metric Cable Length	Cable Type
with Boot				with Heatshrink			
415-0048-012	12"	305 mm	RG-59	415-0047-012	12"	305 mm	Belden 8218
415-0048-024	24"	610 mm	RG-59	415-0047-024	24"	610 mm	Belden 8218
415-0048-036	36"	914 mm	RG-59	415-0047-036	36"	914 mm	Belden 8218
415-0048-048	48"	1219 mm	RG-59	415-0047-048	48"	1219 mm	Belden 8218
415-0048-060	60"	1524 mm	RG-59	415-0047-060	60"	1524 mm	Belden 8218
415-0052-012	12"	305 mm	Belden 734A	415-0049-012	12"	305 mm	Belden 8281
415-0052-024	24"	610 mm	Belden 734A	415-0049-024	24"	610 mm	Belden 8281
415-0052-036	36"	914 mm	Belden 734A	415-0049-036	36"	914 mm	Belden 8281
415-0052-048	48"	1219 mm	Belden 734A	415-0049-048	48"	1219 mm	Belden 8281
415-0052-060	60"	1524 mm	Belden 734A	415-0049-060	60"	1524 mm	Belden 8281
				415-0050-012	12"	305 mm	Commscope 735
				415-0050-024	24"	610 mm	Commscope 735
				415-0050-036	36"	914 mm	Commscope 735
				415-0050-048	48"	1219 mm	Commscope 735
				415-0050-060	60"	1524 mm	Commscope 735
				415-0051-012	12"	305 mm	Belden 735A
				415-0051-024	24"	610 mm	Belden 735A
				415-0051-036	36"	914 mm	Belden 735A
				415-0051-048	48"	1219 mm	Belden 735A
				415-0051-060	60"	1524 mm	Belden 735A
				415-0053-012	12"	305 mm	Belden 1694A
				415-0053-024	24"	610 mm	Belden 1694A
				415-0053-036	36"	914 mm	Belden 1694A
				415-0053-048	48"	1219 mm	Belden 1694A
				415-0053-060	60"	1524 mm	Belden 1694A

SMA Straight Plug to BNC Straight Plug

Connector by Cable Type: **RG-316** (142-0403-011, CPM-88-19) **RG-58** (142-0407-011, CPMC-88-1) **RG-142** (142-0408-011, CPMC-88-13)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0028-MM150	5.9"	150 mm	RG-316
415-0028-006	6"	152 mm	RG-316
415-0028-MM250	9.84"	250 mm	RG-316
415-0028-012	12"	305 mm	RG-316
415-0028-018	18"	457 mm	RG-316
415-0028-MM500	19.7"	500 mm	RG-316
415-0028-024	24"	610 mm	RG-316
415-0028-MM750	29.53"	750 mm	RG-316
415-0028-036	36"	914 mm	RG-316
415-0028-M1.0	39.4"	1000 mm	RG-316
415-0028-048	48"	1219 mm	RG-316
415-0028-M1.5	59.1"	1500 mm	RG-316
415-0028-M2.0	78.7"	2000 mm	RG-316
415-0037-MM250	9.84"	250 mm	RG-58

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0037-012	12"	305 mm	RG-58
415-0037-MM500	19.7"	500 mm	RG-58
415-0037-024	24"	610 mm	RG-58
415-0037-MM750	29.53"	750 mm	RG-58
415-0037-036	36"	914 mm	RG-58
415-0037-M1.0	39.4"	1000 mm	RG-58
415-0037-048	48"	1219 mm	RG-58
415-0037-M1.5	59.1"	1500 mm	RG-58
415-0037-060	60"	1524 mm	RG-58
415-0037-M2.0	78.7"	2000 mm	RG-58
415-0042-012	12"	305 mm	RG-142
415-0042-024	24"	610 mm	RG-142
415-0042-036	36"	914 mm	RG-142
415-0042-048	48"	1219 mm	RG-142
415-0042-060	60"	1524 mm	RG-142

SMA Straight Plug to N Straight Plug

Connector by Cable Type: **RG-58** (142-0407-011, CPN-1) **RG-142** (142-0408-011, CPN-142T)

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0059-MM250	9.84"	250 mm	RG-58
415-0059-012	12"	305 mm	RG-58
415-0059-MM500	19.7"	500 mm	RG-58
415-0059-024	24"	610 mm	RG-58
415-0059-MM750	29.53"	750 mm	RG-58
415-0059-036	36"	914 mm	RG-58
415-0059-M1.0	39.4"	1000 mm	RG-58

Part Number	Standard Cable Length	Metric Cable Length	Cable Type
415-0059-048	48"	1219 mm	RG-58
415-0059-M1.5	59.1"	1500 mm	RG-58
415-0061-060	60"	1524 mm	RG-58
415-0061-012	12"	305 mm	RG-142
415-0061-024	24"	610 mm	RG-142
415-0061-036	36"	914 mm	RG-142
415-0061-048	48"	1219 mm	RG-142
415-0061-060	60"	1524 mm	RG-142



Cinch Connectivity Solutions North America Office

T +1 507.833.8822
ccsorders@us.cinch.com

Cinch Connectivity Solutions Ltd European Office

T +44 (0) 1245 342060
CinchConnectivity@eu.cinch.com

Cinch Connectivity Solutions Asia Pacific Office

T +86 21 5442 7668
ccs.asia.sales@as.cinch.com

Innovative Interconnect Solutions Across the Globe

In operation since 1917, Cinch supplies high quality, high performance connectors and cables globally to the Aerospace, Military/Defense, Commercial Transportation, Oil & Gas, High End Computer, and other markets. We provide custom solutions with our creative, hands on engineering and end to end approach.

Our diverse product offerings include: connectors, enclosures and cable assemblies utilizing multiple contact technologies including copper and fiber optics. Our product engineering and development activities employ cutting edge technologies for design and modeling, and our various technologies and expertise enable us to deliver custom solutions and products for our strategic partnerships. We also serve a broad range of commercial markets, largely through our highly efficient distribution network.

We aim to exceed our customer's expectations, and to continually provide innovative solutions to the rapidly changing needs of the markets, and customers, we serve. For more information, visit cinch.com

