


Pin Header Shrouded 2,54 mm

Series

093



Rated current	3,0 A
Rated voltage	150 V _{RMS} / V _{DC}
Withstand voltage	500 V _{RMS} for one minute
Material contact	Copper alloy
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +105°C
Max. processing temper.	260°C for 10 seconds


All dimensions in mm.

pitch	2,54
termination	
contact size	□ 0,64
max. pincount	064


Product group
3

Variation


PCB Layout






1



2



3



no. of contacts	see figure left	see figure left	available in variation		
n	A	B			
006	15,28	5,08	1	2	3
008	17,82	7,62	1	2	3
010	20,36	10,16	1	2	3
012	22,90	12,70	1	2	3
014	25,44	15,24	1	2	3
016	27,98	17,78	1	2	3
020	33,06	22,86	1	2	3
024	38,14	27,94	1	2	3
026	40,68	30,48	1	2	3
030	45,76	35,56	1	2	3
034	50,84	40,64	1	2	3
040	58,46	48,26	1	2	3
050	71,16	60,96	1	2	3
060	83,86	73,66	1	2	3
064	88,94	78,74	1	2	3

Plating:
T = Sn
F = Au
S = Selective Au

Packaging:
S = Standard
R = Reel

Cap:
0 = Without cap
1 = With cap

Variation (1,2,3)

No. of contacts

Plating contact (T,F,S)

Packaging (S,R)

Cap (0,1)



Order code:

093 - 2 - 2 - 2 - 0 - 2 - 2 - B 2 2

Mating series	101	430
see page	6-9	6-10