


REV.	DATE	DESCRIPTION
NC	08/10/99	INITIAL RELEASE
A	09/26/06	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex						
8						DRAWN	G.R.S.		09/26/06							
7						CHECKED					PART DESCRIPTION SMA FEMALE TO FEMALE R/A ADAPTER					
6						ISSUED										
5						SHEET	1 OF 1				PART NO. 132274					
4	COVER	BRASS	GOLD	1	CAD FILE					DWG. NO. 132274.DWG						
3	CONTACT PIN	BER. COPPER	GOLD	1	C:/132/1132274.DWG											
2	INSULATOR	TEFLON	NATURAL	1						REV.		A	SIZE	A	SCALE	NA
1	BODY	BRASS	GOLD	1												
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING											