


REV.	DATE	ECR NO.	DESCRIPTION
NC	03/16/09	XXXXXX	INITIAL RELEASE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex						
8						DRAWN	CW						08/25/09	
7						CHECKED								
6						ISSUED								
5						SHEET	1 OF 1		PART DESCRIPTION					
4	GASKET	SILICONE	RED	1					N MALE TO FEMALE ADAPTOR					
3	CONTACT PIN	PHOS. BRONZE	GOLD	1					PART NO.					
2	INSULATOR	PTFE	NATURAL	1					172193					
1	BODY	BRASS	NEXCOTE	1					DWG. NO.		172193.DWG	REV. NC	SIZE A	SCALE NA
	DESCRIPTION	MATERIAL	FINISH	QTY					CAD FILE					
								C:/CONNEX/172193.DWG						