






Board  
mounting hole

Panel thickness 1,6 mm


Board  
mounting hole

Panel thickness 1,0 - 1,8 mm




A

| Part No.        | "A"<br>mm | "B"<br>mm |
|-----------------|-----------|-----------|
| HLCBSE-2-4M-01  | 4.0       | 10.0      |
| HLCBSE-2-6M-01  | 6.0       | 12.0      |
| HLCBSE-2-8M-01  | 8.0       | 14.0      |
| HLCBSE-2-10M-01 | 10.0      | 16.0      |
| HLCBSE-2-12M-01 | 12.0      | 18.0      |
| HLCBSE-2-14M-01 | 14.0      | 20.0      |
| HLCBSE-2-25M-01 | 25.0      | 31.0      |
| HLCBSE-2-30M-01 | 30.0      | 36.0      |

**HLCBSE-2****HLCBSE-2/PCBEHE-2**

HINGED CIRCUIT BOARD SUPPORT SYSTEM

| Part No.        | "A"<br>mm |
|-----------------|-----------|
| PCBEHE-2-4M-01  | 4.0       |
| PCBEHE-2-6M-01  | 6.0       |
| PCBEHE-2-8M-01  | 8.0       |
| PCBEHE-2-10M-01 | 10.0      |
| PCBEHE-2-12M-01 | 12.0      |
| PCBEHE-2-14M-01 | 14.0      |
| PCBEHE-2-25M-01 | 25.0      |
| PCBEHE-2-30M-01 | 30.0      |

**PCBEHE-2**

Note:

|        |      |        |               |
|--------|------|--------|---------------|
| HLCBSE | 2    | 10M    | 01            |
| Part   | Type | Length | Material Code |

Material: Nylon 6/6 - natural; UL 94 V-2, RMS-01  
by special order:  
Nylon 6/6 - natural; UL 94 V-0, RMS-19  
Std. Pk.: 1.000 pcs.

Note:

|        |      |        |               |
|--------|------|--------|---------------|
| PCBEHE | 2    | 10M    | 01            |
| Part   | Type | Length | Material Code |