





P/N	GOLD PLATING ON CONTACT AREA
1050480001	0.375um (15u") MIN

NOTE:

- MATERIAL
HOUSING : LIQUID CRYSTALLINE POLYMER (LCP), GLASS FILLED
UL94V-0, COLOR: BLACK
TERMINAL : PHOSPHOR BRONZE
SHELL : STAINLESS STEEL
- FINISHES
TERMINAL : 0.375um (15u") MIN GOLD ON CONTACT AREA
0.0762 - 0.127um (3 - 5u") GOLD FLASH ON SOLDER TAILS
1.27um (50u") MIN NICKEL UNDERPLATE OVER ALL
SHELL : 0.0762um (3u") MIN GOLD FLASH OVER 1.27um (50u") MIN
NICKEL UNDERPLATE ON SOLDER AREAS
- PRODUCT SPECIFICATION: PS-105048-001
- PACKAGING SPECIFICATION: PK-105048-001
- ALL SOLDER TAILS COPLANARITY: 0.08mm MAX
- COMPLIANT TO RoHS DIRECTIVE 2002/95/EC & ELV DIRECTIVE 2000/53/EC
- DATE CODE *** (4 DIGITS)
DAY
WEEK
YEAR



DELETED P/N EC NO: SH2011-0217 DRWN: JZENG CHKD: APPR: KHLIM REV	2011/02/24 2011/03/07 DESCRIPTION	QUALITY SYMBOLS FA=0 FC=0 FP=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION								
				mm	INCH	DRAWN BY HJWANG02	DATE 2009/02/04	TITLE 1.45MM LOW PROFILE SIM 6 PINS WITH GUIDE RAIL									
			4 PLACES	± ---	± ---	CHECKED BY YLZHU	DATE 2009/02/04										
			3 PLACES	± ---	± ---	APPROVED BY SKTOH					DATE 2010/04/19						
			2 PLACES	± 0.15	± ---												
			1 PLACE	± 0.20	± ---	MATERIAL NO.					DOCUMENT NO.					SHEET NO. 1 OF 1	
ANGULAR ± 3 °																	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-105048-001												
A3			A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												