







Specifications

- **Certifications*:** UL, CSA, VDE, TUV, SEMKO, DEMKO, NEMKO, FIMKO, SEVand BEAB
- **Dielectric Strength:** 1,000 V (minimum)
- **Insulation Resistance:** 100 Megohms (minimum)
- **Base Material:** Nylon
- **Actuator Material:** Polyester or Nylon

Dimensional Specifications: in. [mm]

[illegible]

Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.

- 1 Additional ratings are available. Consult factory.
Rating 22 must use circuit D only and momentary rocker.
- 2 Matte finish is standard. Custom colors are available. Consult factory.
- 3 Molded-in Legend available only with Visi-Rocker option.
- 4 White is standard with dark actuators; black is standard with light actuators.