


REV.	DATE	DESCRIPTION
NC	07/24/07	INITIAL RELEASE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS	DATE	Amphenol Connex					
8						DRAWN	G.R.S.						07/24/07
7						CHECKED			PART DESCRIPTION BNC PLUG TO 1.0/2.3 FEMALE ADAPTER				
6						ISSUED							
5						SHEET	1 OF 1		PART NO. 242231–75				
4													
3	CONTACT PIN	BER. COPPER	GOLD	1				PART NO. 242231–75					
2	INSULATOR	TEFLON	NATURAL	1									
1	BODY	BRASS	GOLD	1				DWG. NO. 242231–75.DWG REV. NC SIZE A SCALE NA					
	DESCRIPTION	MATERIAL	FINISH	QTY									
					DO NOT SCALE DRAWING	C:/242/242231–75.DWG							