

NFT3-__ __ (color)

Specifications

Description: Rail mount terminal block.

Rating: 40A, 600V
55A Factory
Wired



Center Spacing: 0.390" (9.91 mm)

Number of Poles: 3

Circuits Per Foot: 28

Circuit Jumper: JN3, 2 circuits

Wire Range: AWG #8-22 Cu

Screw Size: #8-32

Mounting Options: C-rail

Marking Tape: MT12-1-2

Torque Rating: 18 lb-in

Operating Temperature: 105°C


Agency Information: UL File E62622,
CSA File 47235.

Catalog Numbers

Catalog

Numbers	Colors
NFT3-WH	White (Standard)
NFT3-BK	Black
NFT3-BL	Blue
NFT3-RE	Red
NFT3-YE	Yellow

Dimensions - in (mm)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cooper Bussmann:

[NFT3-BL](#) [NFT3-RE](#) [NFT3-YE](#)