



Part Number	Length (inch)	Length (mm)
1366-C-24	24	609,4
1366-C-36	36	914,4
1366-C-48	48	1219.2

FEATURES:

- Model 1366-C provides a simple means to connect between equipment with both BNC and Type N input jacks.
- Both connectors feature nickel plated shells to provide the greatest tarnish resistance.
- Gold plated center conductors assure noise free connections..

MATERIALS:

Type N Male: Body and Fittings – Brass, Tarnish Resistant

Center Conductor – Brass, Gold Plated

Impedance: 50 Ohms

Cable: RG58C/U, Impedance 50 Ohms, O.D. .195" 5,0mm

BNC Male: Body and Fittings – Brass, Tarnish Resistant

Center Contact – Brass, Gold Plated

Impedance: 50 Ohms

RATINGS:

Operating Voltage: 500 VRMS

Operating Temperature: +80°C (+176°F) Max.

ORDERING INFORMATION: Model 1366-XX

XX = Length in inches. Additional lengths can be quoted upon request.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[1366-C-36](#) [1366-C-24](#) [1366-C-48](#)