




(2,00 mm) .0787"



TMM SERIES

# LOW PROFILE SMT HEADER

## SPECIFICATIONS

For complete specifications and recommended PCB layouts see [www.samtec.com?TMM](http://www.samtec.com?TMM)

**Insulator Material:** Black Liquid Crystal Polymer

**Terminal Material:** Phosphor Bronze

**Plating:** Sn or Au over 50µ" (1,27 µm) Ni

**Current Rating:** 3.2 A per pin (1 pin powered per row)

**Operating Temp Range:** -55°C to +105°C with Tin; -55°C to +125°C with Gold

**Voltage Rating:** 500 VAC mated with SQW 450 VAC mated with SQT

**RoHS Compliant:** Yes

**Processing:** Lead-Free Solderable: Yes


**SMT Lead Coplanarity:** (0,15 mm) .006" max

**Mates with:**

CLT, SQT, SQW, ESQT, TLE, SMM, MMS, TCSD



## OTHER SOLUTIONS

**Through-Hole**



### 2 mm Shunt

Specify **2SN-BK-G** for 2 mm shunt with Gold plating.



Available with optional

- Pick & Place Pads
- Alignment pins
- Tape & reel packaging

## RECOGNITIONS

For complete scope of recognitions see [www.samtec.com/quality](http://www.samtec.com/quality)



## ALSO AVAILABLE (MOQ Required)

- Other platings
- Contact Samtec.

**TMM** — **1** **NO. PINS PER ROW** — **LEAD STYLE** — **PLATING OPTION** — **ROW OPTION** — **SM** — **OTHER OPTION**

02 thru 40

Specify **LEAD STYLE** from chart below.

**-F**  
= Gold flash on post, Matte Tin on tail

**-L**  
= 10µ" (0,25 µm) Gold on post, Matte Tin on tail

**-S**  
= 30µ" (0,76 µm) Gold on post, Matte Tin on tail

**-T**  
= Matte Tin

**-S**  
= Single Row

**-D**  
= Double Row

**-A**  
= Alignment Pin (Metal or plastic at Samtec's discretion) (5 positions minimum) (-D only)





**-“XXX”**  
= Polarized Position (Specify position of omitted pin)

**-M**  
= Metal Pick & Place Pad (4 positions minimum) (-T plating not available) (-D only)

**-P**  
= Pick & Place Pad (3 positions minimum)

**-TR**  
= Tape & Reel Packaging (3 thru 36 positions only)

| LEAD STYLE | A           | MATES WITH                          |
|------------|-------------|-------------------------------------|
| -01        | (3,20) .126 | SQT, SQW, ESQT, TLE, SMM, MMS, TCSD |
| -04        | (1,91) .075 | CLT                                 |
| -05        | (1,65) .065 |                                     |
| -06        | (4,27) .168 | CLT-BE                              |



**Note:** Some lengths, styles and options are non-standard, non-returnable.