





20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5
	STANDARD SOLDER TAILS					LONG SOLDER TAILS					PRESS-FIT TAILS				
# CKT	PART NUMBER	DIM "A" ±0.25/±.010	DIM "C" ±0.25/±.010			PART NUMBER	DIM "A" ±0.25/±.010	DIM "C" ±0.25/±.010			PART NUMBER	DIM "A" ±0.25/±.010	DIM "C" ±0.25/±.010		
10	46436-9010	57.00/2.244	2.84/1.12			46436-9110	57.00/2.244	3.61/1.42			46436-9210	57.00/2.244	3.28/1.29 (COMPLIANT TAILS DESIGNED FOR MIN. 1.58/0.062" THICK PCB)		
9	46436-9009	51.50/2.028				46436-9109	51.50/2.028				46436-9209	51.50/2.028			
8	46436-9008	46.00/1.811				46436-9108	46.00/1.811				46436-9208	46.00/1.811			
7	46436-9007	40.50/1.594				46436-9107	40.50/1.594				46436-9207	40.50/1.594			
6	46436-9006	35.00/1.378				46436-9106	35.00/1.378				46436-9206	35.00/1.378			
5	46436-9005	29.50/1.161				46436-9105	29.50/1.161				46436-9205	29.50/1.161			
4	46436-9004	24.00/0.945				46436-9104	24.00/0.945				46436-9204	24.00/0.945			
3	46436-9003	18.50/0.728				46436-9103	18.50/0.728				46436-9203	18.50/0.728			
2	46436-9002	13.00/0.512				46436-9102	13.00/0.512				46436-9202	13.00/0.512			
1	46436-9001	7.50/0.295				46436-9101	7.50/0.295				46436-9201	7.50/0.295			





P/N: 46436-9005 SHOWN



RECOMMENDED LAY-OUT AND KEEP-OUT ZONE



P/N: 46436-9005 SHOWN



NOTES:

- MATERIAL:
 - HOUSINGS: LCP UL-94, V-0, COLOR: BLACK.
 - TERMINALS: COPPER ALLOY.
 - PLATING: 0.00127/0.00050 NICKEL OVERALL WITH 0.00254/0.00100 SELECTIVE MATTE TIN ON TAILS AND 0.000762/0.00030 SELECTIVE GOLD ON CONTACT AREA.
- PACKAGING: ASSEMBLIES TO BE TRAY PACKED PER PACKAGING SPEC PK-46436-xxx.
- PRODUCT SPEC: PS-46436-100.
- APPLICATION SPEC: AS-46436-100.
- ASSEMBLY MATES TO MOLEX PLUG ASSEMBLY 46437- SERIES: CONTACT MOLEX FOR DETAILS.

ADD VIEWS EC NO: UCP2011-3988 DRAWN BY: CHYDROBOSTIC CHECKED BY: APPR: RIELSON DATE: 2011/06/16 DATE: 2011/06/21	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 3:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
		4 PLACES	± ---	± ---	mm	INCH	DRAWN BY BKOSTIC		DATE 2008/04/24	TITLE DC POWER RECEPTACLE MOD TEN60, 5.5 PITCH R/A 1-10 CKT
		3 PLACES	± ---	± .010	mm	INCH	CHECKED BY BKOSTIC		DATE 2008/04/24	
		2 PLACES	± 0.25	± .010	mm	INCH	APPROVED BY APATEL		DATE 2008/06/30	
		1 PLACE	± 0.25	± .010	mm	INCH	MATERIAL NO. SEE CHART		DOCUMENT NO. SD-46436-9000	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		ANGULAR ±1/2°		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				