







Material:

- Housing: PBT+30% Glass Filled, UL94V-0 Black
- Shell: SPCC, Nickel plating
- Terminal: Phosphor Bronze, Gold plated on contact area, Tin plating on solder tail

Specification:

- Current rating: 1.0A Max
- Contact Resistance: 40MΩ Max
- Insulation Resistance: 100MΩ Min. @500V DC
- Dielectric Withstanding: 500V AC for 1 min.
- Operating Temperature: -20°C ~ +70°C

Unit: MM±0.25MM

Scale	1:1							Name
TOLERANCE						Drawn	10.19.11	Chappell
X.X	±0.40					Approved		
X.XX	±0.25							
X.XXX	±0.15							
Angle	±3°							
			Modification	Date	Name			

Item No.	
A-USB-A-2P-RJ45-0-R	
Title Connector USB2.0 2-Port + RJ45 port - 10/100, Female w/2 LED & Transformer, Non-Filter, Shielded	
Drawing No.	rev00
Replace	Sheet

