


PIN RECEPTACLES

**FOR .008" - .013" DIAMETER PINS (#04 CONTACT)
AND .012" - .017" DIAMETER PINS (#10 CONTACT)
(SEE SPECIFIC CONTACT RANGE ON PAGE 250)**

8210

8210-0-15-15-04-27-04-0


Press-fit in .024/.027 stepped hole



0439

0439-0-15-15-04-27-04-0


Press-fit in .025 mounting hole



X464

X464-X-15-XX-10-XX-04-0

Solder mount in .016 min. mounting hole




Basic Part Number	Length A
0464-0	.125
0464-1	.250
6464-0	.275

9225

9225-0-15-XX-10-XX-10-0


Press-fit in .039 mounting hole



0529

0529-0-15-XX-10-XX-10-0


.040 min. mounting hole



8947

8947-0-15-XX-10-XX-10-0


Solder mount in .040 min. mounting hole



4993

4993-0-15-15-10-27-10-0

Compliant press-fit in .041 - .043 Dia. mounting hole



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$

Diameters: $\pm .002$

Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

01 200 μ " TIN/LEAD OVER NICKEL

◆ **80** 200 μ " TIN OVER NICKEL (RoHS)

◆ **15** 10 μ " GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

02 100 μ " TIN/LEAD OVER NICKEL

◆ **84** 100 μ " TIN OVER NICKEL (RoHS)

◆ **27** 30 μ " GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#04 or #10 CONTACT (DATA ON PAGE 250)
(CONTACTS #04 & #10 NOT INTERCHANGEABLE)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com