





Light Bars

Shape	Part Number	Emitting Color	Emitting Material	Lens-Color	Wave Length (nm)	Luminous Intensity IF=20mA (mcd) Min. Max.	Figure No.
8.89x3.81mm	EUR2300M	Red	GaAsP/GaP	White Diffused	625	10 - 25	1
	EMRA100M	Red	GaAlAs	White Diffused	660	40 - 75	
	EMG2500D	Green	GaP	Green Diffused	565	10 - 25	
	EUY2400M	Yellow	GaAsP/GaP	White Diffused	590	8 - 18	
19.05x3.81 mm	EUR2350M	Red	GaAsP/GaP	White Diffused	625	20 - 50	2
	EMRB100M	Red	GaAlAs	White Diffused	660	30 - 80	
	EMG2550D	Green	GaP	Green Diffused	565	20 - 50	
	EUY2450M	Yellow	GaAsP/GaP	White Diffused	590	15 - 38	
8.89x8.89mm	EUR2655M	Red	GaAsP/GaP	White Diffused	625	20 - 45	3
	EMRC100M	Red	GaAlAs	White Diffused	660	30 - 80	
	EMG2855D	Green	GaP	Green Diffused	565	20 - 50	
	EUY2755M	Yellow	GaAsP/GaP	White Diffused	590	15 - 35	
8.89x3.81 mm	EUR2600M	Red	GaAsP/GaP	White Diffused	625	10 - 25	4
	EMRD100M	Red	GaAlAs	White Diffused	660	45 - 75	
	EMG2800D	Green	GaP	Green Diffused	565	10 - 25	
	EUY2700M	Yellow	GaAsP/GaP	White Diffused	590	8 - 18	



Package Dimensions Units :mm
Tolerance : .25mm (0.01")