



WIRE RANGE	IL E13288 Listed
12-10 AWG STRANDED	12-10 AWG STRANDED
IL LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

△ STAMP AMP 12-10* APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± - ANGLES

DR 2-9-93
TA BRINKMAN
CHK 2-9-93
DA PATTERSON
APD 2-9-93
DE MILLER
APD 2-9-93
JL NECKLEY
PRODUCT SPEC

AMP
AMP Incorporated
Harrisburg, PA 17105-3508

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS
1-800-522-6752

VOLTAGE RATING: NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.64mm² [5,180-13,100] CIR MILS STRANDED

FINISH TIN PLATE
0.00254[1.000100] MIN THK PER MIL-T-10727

TERMINAL, RING TONGUE, BUDGET

FOR APPLICATION TOOLING INFORMATION
1-800-722-1111

WIRE CROSS SECTIONAL AREA RANGE: 2.62-6.64mm² [5,180-13,100] CIR MILS STRANDED

FINISH TIN PLATE
0.00254[1.000100] MIN THK PER MIL-T-10727

APD 2-9-93
DE MILLER
APD 2-9-93
JL NECKLEY
PRODUCT SPEC

SIZE CAGE CODE DRAWING NO
00779 320761