





REV	DESCRIPTION	DET	DATE
D	ITEM 3, 130053 WAS 123189	EL	11/10/11
E	128528C WAS 128638C. ADDED 128487	JJC	08/03/12
F	ADDED 508511, 130322CS WAS 127582, 130326 WAS 126745; ADDED .430 & .536; ADDED VIEW; ADDED PATENT ETCH	NDG	06/19/13



NOTES:

- 1 MAXIMUM RECOMMENDED STROKE .500
- 2 FOR USE WITH THE 206-375 TOOL. FOR OTHER TOOLS AND/OR STROKE COMBINATIONS, REFER TO THE STROKE LIMITER CHART (HK1122) OR CONSULT AN AFS/HUCK SPECIALIST.
- 3 SHIP WITH: STOP 126747, DEFLECTOR 126748-3 AND (2) .030 SHIMS 128290 REFERENCE PB563 FOR PROPER USE.
- 4 128638C ASSEMBLY CONSISTS OF 128528C COLLET AND 128487 DRAWBAR.

ETCH "U.S. PATENT #6739170" WHERE SHOWN

F	508511	2	#6-32 B.H.C.S.	10
	128487	1	DRAWBAR	9
	126748-3	1	UNITIZED DEFLECTOR	8
F	128528C	1	COLLET	7
	130326	1	GUARD	6
	120095	1	DEFLECTOR	5
F	122727-1	1	BARBED RETAINER	4
	130053	1	UNITIZED CHUCK JAW	3
	130322CS	1	TOP GUARD	2
	12711C	1	ANVIL	1
	PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC 42-311: ★ ETCH	HUCK INTERNATIONAL, INC., I.S.D 1 CORPORATE DR KINGSTON, NEW YORK 12401		
ITAR/ECCN: EAR99	CLEARANCE NOSE ASSEMBLY -05 MGP STRADDLE		
SCH B#: 8467.99.0190	FINAL ASSY: FOR USE WITH 206-375		
HTS: 8467.99.0190	ENG: MVM CK:	DATE: 10/21/04	SCALE: 2:1
	B	99-3749C	