





CAPACITANCE	3000pF GMV
TEMP. RANGE	-55°C/+125°C
CURRENT	25 AMPS
WORKING VOLTAGE	85°C 700 VDC 125°C 500 VDC
IL=PER MIL-STD-220 @ 25°C	
FREQ. MHz	I.L. (db)
10	8
100	50
1 GHz	70
10 GHz	70

SCHEMATIC



MARKING:

PART: NONE
 FOAM PACK: SCI
 1204-050
 DATE CODE
 LOT No.
 QTY./PACK

	8	7	6	5	4	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED		api  technologies corp.		FAIRVIEW PENNSYLVANIA	
	CN 70724-ENG	CN 30156-CPD	CN 214017	CN 207017	CN 172577 REDRAWN	CHANGE NOTICE	Fractions $\pm 1/64$		Dwn. KEVERLINE	Description		
							Dec. .xx $\pm$		Date 8-21-06	Pi, EYELET STYLE FILTER		
							Dec. .xxx $\pm .010$		Engr. T. TAYLOR			
							Angles $\pm 0^{\circ} 30'$		Scale NONE			
							CODE IDENT. NO. 0LSP2				1204-050	

