

2-conductor fuse disconnect terminal block with pivoting fuse holder; for 5 x 20 mm miniature metric fuse; without blown fuse indication

Item No.: 2002-1611



2-conductor fuse disconnect terminal block with pivoting fuse holder; for 5 x 20 mm miniature metric fuse; without blown fuse indication

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	2002-1611
GTIN / EAN	4045454974732
Content	1
Order amount	50
Customer item number	

Notes


Technical data



Miscellaneous

Total number of connection points	2
Total number of potentials	1
Color	gray
Ratings according to 1	IEC/EN 60947-7-3
Pollution degree (1)	3
Rated voltage EN (1) [V]	250 [V]
Rated surge voltage (1) [kV]	6 [kV]
Nominal current [A]	6.3 [A]

Technical data	
Connection technology (1)	Push-in CAGE CLAMP®
Nominal cross section 1	2.5 mm ²
Solid sizes 1	0.25 ... 4 mm ² / 22 ... 12 AWG
solid, directly pluggable 1	0.75 ... 4 mm ² / 18 ... 12 AWG
Fine-stranded wires 1	0.25 ... 4 mm ² / 22 ... 12 AWG
min. fine-stranded with insulated ferrule, push-in terminati	0.75 mm ² / 18 AWG
Strip length 1	10 ... 12 mm / 0.39 ... 0.47 in
Type of wiring	Front-entry wiring
Design	horizontal
Marking level	Center/Side marking
Insulating material	Polyamide 66 (PA 66)
Fire load [MJ]	0.282 [MJ]
Weight [g]	13.239 [g]
Width	6.2 mm / 0.244 in
Height from upper-edge of DIN-rail [mm]	57.2 [mm]
Height from upper-edge of DIN-rail	57.2 mm / 2.252 in
Length	66.1 mm / 2.602 in
Type of mounting	DIN 35 rail
Safety information 1	Electrical ratings are given by the fuse.

Images & drawings





Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.