


Surface Mount LED J Series for low current or superbright use, 0178 Series “0805” Package



The 0178 series lamps are miniature chip type designed for surface mounting. These lamps are of the so-called 0805 size, measuring approximately 1.25 x 2.0 mm. These lamps are in EIA481 tape and reel packaging with approximately 3000 pcs per reel.



GENERAL INFORMATION

Operating Temperature Range	-40 °C to +85 °C
Storage Temperature Range	-40 °C to +90 °C
Reflow Soldering Temperature	260 °C for 5 sec max

APPLICATION INFORMATION (ALL RATINGS AT 25 °C AMBIENT)

Part No.	Emitted Color	Peak	$\Delta\lambda$	Absolute Maximum Ratings					E/O Characteristics					
		λ		Pd	If (mA)		Ir	Vr	Iv (mcd) @ If=20mA			Vf (V) @ If=20mA		2 $\Theta_{1/2}$
		(nm)		(mW)	dc	1/10 duty @ 1 kHz	@ Vr=5V (μ A)	(V)	2mA	Min	Typ	Min	Typ	(Deg)
JRC0178	Red	632	20	60	25	160	10	5	3	17	42	2.0	2.4	140
JGC0178	Green	575	20	60	25	160	10	5	1	12	17	2.0	2.4	140
JYC0178	Yellow	591	15	60	25	160	10	5	3	17	43	2.0	2.4	140
JOC0178	Orange	621	18	60	25	160	10	5	3	17	43	2.0	2.4	140
JEC0178	OrRed	639	20	60	25	160	10	5	2	16	34	2.0	2.4	140
JYOC0178	YelOrng	611	17	60	25	160	10	5	3	17	43	2.0	2.4	140

Specifications subject to change without notice. Dimensions are in mm $\pm$ 0.3 unless stated otherwise.

IDEA, Inc., 1300-B Pioneer St., Brea, CA 92821

Ph:562-697-4332, 800-LED-IDEA; Fax: 562-690-1352 013S-J0178