


LDC Series Triple Output —
15-60 Watts Open Frame, Universal Input AC 85~264




Designed for Low Profile and Low Cost.

- Low Profile Lightweight PC Board Construction, Low Cost
- High Quality — Field Failure Rate Less than 0.012%
- Universal Input: AC 85-264
- Inrush Current, Over-Voltage and Over-Current Protection Circuitry
- Fully Regulated, Fully Isolated Input/Output, V1 Isolated From V2 and V3
- Zero Minimum Load


- Available with Chassis and Cover Option (SN Option)
- Also Available with ±10% Voltage Adjustable Output Potentiometer (Y Option)
- Conductive Noise: FCC-B, VCCI-2 and VFG 243/91
- UL, CSA and TUV Safety Approvals, CE Marked
- Two Year Warranty
- Wiring Harnesses Available on Bottom of Page 696

Stock No.	Mfr.'s Type	Watts Approx.	DC Output (V)/Current (A)			Dimensions W × H × D (In.)	Weight (Lbs.)	EACH	
			V1	V2	V3			1-4	5-24
800-9280	LDC15F-1	16.0	+5 V/2.0 A (Pk 3.0)	+12 V/0.3 A (Pk 0.6)	-12 V/0.2 A (Pk 0.30)	1.97 × 1.02 × 5.00	0.33	50.76	46.90
800-0380	LDC15F-1-SN	16.0	+5 V/2.0 A (Pk 3.0)	+12 V/0.3 A (Pk 0.6)	-15 V/0.2 A (Pk 0.30)	2.25 × 1.50 × 5.79	0.66	57.14	55.30
800-9285	LDC15F-2	17.5	+5 V/2.0 A (Pk 3.0)	+15 V/0.3 A (Pk 0.6)	-15 V/0.2 A (Pk 0.30)	1.97 × 1.02 × 5.00	0.33	50.76	46.90
800-0385	LDC15F-2-SN	17.5	+5 V/2.0 A (Pk 3.0)	+15 V/0.3 A (Pk 0.6)	-15 V/0.2 A (Pk 0.30)	2.25 × 1.50 × 5.79	0.66	57.14	55.30
800-9290	LDC30F-1	3.3	+5 V/3.0 A (Pk 4.5)	+12 V/1.2 A (Pk 2.0)	-12 V/0.3 A (Pk 0.45)	2.56 × 1.02 × 5.51	0.48	71.86	66.40
800-0390	LDC30F-1-SN	3.3	+5 V/3.0 A (Pk 4.5)	+12 V/1.2 A (Pk 2.0)	-12 V/0.3 A (Pk 0.45)	2.84 × 1.50 × 6.30	0.88	75.71	73.27
800-9295	LDC30F-2	34.5	+5 V/3.0 A (Pk 4.5)	+15 V/1.0 A (Pk 2.0)	-15 V/0.3 A (Pk 0.45)	2.56 × 1.02 × 5.51	0.48	71.86	66.40
800-0395	LDC30F-2-SN	34.5	+5 V/3.0 A (Pk 4.5)	+15 V/1.0 A (Pk 2.0)	-15 V/0.3 A (Pk 0.45)	2.84 × 1.50 × 6.30	0.88	75.71	73.27
800-4020	LDC60F-1	61.0	+5 V/5.0 A (Pk 7.0)	+12 V/2.5 A (Pk 3.5)	-12 V/0.5 A (Pk 0.70)	3.27 × 1.02 × 7.28	0.66	111.09	102.64
800-0400	LDC60F-1-SN	61.0	+5 V/5.0 A (Pk 7.0)	+12 V/2.5 A (Pk 3.5)	-12 V/0.5 A (Pk 0.70)	3.62 × 1.50 × 8.27	1.21	114.29	110.60
800-4025	LDC60F-2	62.5	+5 V/5.0 A (Pk 7.0)	+15 V/2.0 A (Pk 3.5)	-15 V/0.5 A (Pk 0.70)	3.27 × 1.02 × 7.28	0.66	111.09	102.64



PMC Series Triple Outputs —
15-100 Watts Metal Chassis Mount, Wide Range Input AC 85~264

Designed for High Reliability and Compact Footprint.



- Chassis Mount, Compact Footprint
- High Quality — Field Failure Rate Less than 0.012%
- Universal Input: AC 85-264
- User Selectable Input: AC 85-132, 170-264
- Inrush Current, Over-Voltage and Over-Current Protection Circuitry
- Fully Regulated, Fully Isolated Input/Output, V1 Isolated from V2 and V3
- Built-In ±10% Voltage Adjustable Potentiometer on V1
- Zero Minimum Load
- Available with Cover Option (N Option) PMC 50, 75 and 100
- Conductive Noise: FCC-B
- UL, CSA and TUV Safety Approvals, CE Marked
- Three Year Warranty
- Wiring Harnesses Available on Bottom of Page 696

Stock No.	Mfr.'s Type	Watts Approx.	Output (V)/Current (A)			Dimensions W × H × D (In.)	Weight (Lbs.)	EACH	
			V1	V2	V3			1-4	5-24
800-1160	PMC15E-1	15	5 V/2 A	12 V/0.30 A	-12 V/0.20 A	1.46 × 2.36 × 4.33	0.55	73.00	67.00
800-1170	PMC15E-2	15	5 V/2 A	15 V/0.30 A	-15 V/0.20 A	1.46 × 2.36 × 4.33	0.55	68.67	63.45
800-1180	PMC15E-3	15	5 V/2 A	12 V/0.30 A	-5 V/0.20 A	1.46 × 2.36 × 4.33	0.55	68.67	63.45
800-1190	PMC30E-1	30	5 V/3 A	12 V/1.20 A	-12 V/0.30 A	1.52 × 2.36 × 5.71	0.66	92.15	85.15
800-1200	PMC30E-2	30	5 V/3 A	15 V/0.70 A	-15 V/0.50 A	1.52 × 2.36 × 5.71	0.66	92.15	85.15
800-1210	PMC30E-1-XULA-N	50	5 V/5 A	12 V/1.25 A	-12 V/0.35 A	1.34 × 3.66 × 7.28	0.88	131.53	121.53
800-1240	PMC75E-1-N	75	5 V/8 A	12 V/2.50 A	-12 V/0.50 A	1.65 × 3.66 × 8.07	1.32	181.00	167.25
800-1250	PMC75E-2-N	75	5 V/8 A	15 V/1.80 A	-15 V/0.50 A	1.65 × 3.66 × 8.07	1.32	181.01	167.25
800-1260	PMC75E-4-N	75	5 V/6 A	12 V/3.20 A	-12 V/0.50 A	1.65 × 3.66 × 8.07	1.32	181.01	160.38
800-1270	PMC100E-1-N	100	5 V/13 A	12 V/2.00 A	-12 V/1.00 A	1.89 × 3.66 × 8.66	1.65	211.05	195.01
800-1280	PMC100E-2-N	100	5 V/13 A	15 V/1.50 A	-15 V/1.00 A	1.89 × 3.66 × 8.66	1.65	211.05	195.01
800-1290	PMC100E-4-N	100	5 V/8 A	12 V/4.00 A	-12 V/1.00 A	1.89 × 3.66 × 8.66	1.65	211.05	195.01

12

RMC and MMC Series Triple Outputs —
8-100 Watts Metal Chassis Mount, Standard Input AC 85~132




Designed for High Reliability and Compact Footprint.

- Chassis Mount, Compact Footprint
- High Quality — Field Failure Rate Less than 0.012%
- Standard Input: AC 85-132
- Inrush Current, Over-Voltage and Over-Current Protection Circuitry
- Fully Regulated, Fully Isolated Input/Output, V1 Isolated from V2 and V3
- Built-In ±10% Output Voltage Adjustment Potentiometer on V1

- Zero Minimum Load
- Available with Cover Option (N Option)
- Conductive Noise: FCC-B, Some Models FCC-A
- UL and CSA Safety Approvals
- Two Year Warranty
- Wiring Harnesses Available on Bottom of Page 696

Stock No.	Mfr.'s Type	Watts Approx.	Output (V)/Current (A)			Dimensions W × H × D (In.)	Weight (Lbs.)	EACH	
			V1	V2	V3			1-4	5-24
800-1801	MMC8A-1-N	8	+5 V/1.2 A	+12 V/0.1 A	-12 V/0.1 A	1.06 × 2.91 × 2.68	0.33	45.44	41.99
800-1806	MMC8A-2-N	8	+5 V/1.1 A	+15 V/0.1 A	-15 V/0.1 A	1.06 × 2.91 × 2.68	0.33	45.44	41.99
800-1811	MMC8A-3-N	8	+5 V/1.2 A	+12 V/0.1 A	-5 V/0.1 A	1.06 × 2.91 × 2.68	0.33	45.44	41.99
800-8061	RMC15A-1-N	15	+5 V/2.0 A	+12 V/0.3 A	-12 V/0.2 A	1.26 × 3.14 × 3.93	0.55	56.29	52.01
800-8066	RMC15A-2-N	15	+5 V/2.0 A	+15 V/0.2 A	-15 V/0.2 A	1.26 × 3.14 × 3.93	0.55	56.29	52.01
800-8071	RMC30A-1-N	30	+5 V/3.0 A	+12 V/1.2 A	-12 V/0.3 A	1.37 × 3.14 × 5.31	0.77	75.48	69.75
800-8076	RMC30A-2-N	30	+5 V/3.0 A	+15 V/0.5 A	-15 V/0.5 A	1.37 × 3.14 × 5.31	0.77	75.48	69.75
800-1836	MMC50A-1-N	50	+5 V/5.0 A	+12 V/2.0 A	-12 V/0.5 A	1.42 × 3.66 × 6.10	0.88	109.82	101.47
800-1841	MMC50A-2-N	50	+5 V/5.0 A	+15 V/1.2 A	-15 V/0.5 A	1.42 × 3.66 × 6.10	0.88	109.82	101.47
800-1846	MMC50A-3-N	50	+5 V/5.0 A	+12 V/2.0 A	-5 V/0.5 A	1.42 × 3.66 × 6.10	0.88	109.82	101.47
800-1851	MMC50A-4-N	50	+5 V/7.0 A	+12 V/1.5 A	-12 V/0.3 A	1.42 × 3.66 × 6.10	0.88	109.82	101.47
800-0006	RMC50A-1-N	50	+5 V/5.0 A	+12 V/2.0 A	-12 V/0.5 A	1.37 × 3.66 × 6.10	0.77	98.97	91.44
800-1266	RMC50A-2-N	50	+5 V/5.0 A	+15 V/1.2 A	-15 V/0.5 A	1.37 × 3.66 × 6.10	0.77	98.97	91.44
800-1856	MMC75A-1-N	75	+5 V/8.0 A	+12 V/2.5 A	-12 V/0.5 A	1.65 × 3.66 × 6.89	1.32	159.29	147.18
800-1861	MMC75A-2-N	75	+5 V/8.0 A	+15 V/1.8 A	-15 V/0.5 A	1.65 × 3.66 × 6.89	1.32	159.29	147.18
800-1866	MMC75A-3-N	75	+5 V/8.0 A	+12 V/2.5 A	-5 V/0.5 A	1.65 × 3.66 × 6.89	1.32	159.29	147.18
800-1871	MMC75A-4-N	75	+5 V/6.0 A	+12 V/3.2 A	-12 V/0.5 A	1.65 × 3.66 × 6.89	1.32	159.29	147.18
800-1876	MMC100A-1-N	100	+5 V/13.0 A	+12 V/2.0 A	-12 V/1.0 A	1.97 × 3.66 × 7.48	1.54	184.04	170.06
800-1881	MMC100A-2-N	100	+5 V/13.0 A	+15 V/1.5 A	-15 V/1.0 A	1.97 × 3.66 × 7.48	1.54	184.00	180.00
800-1886	MMC100A-3-N	100	+5 V/13.0 A	+12 V/2.0 A	-5 V/1.0 A	1.97 × 3.66 × 7.48	1.54	184.04	170.06
800-1891	MMC100A-4-N	100	+5 V/8.0 A	+12 V/4.0 A	-12 V/1.0 A	1.97 × 3.66 × 7.48	1.54	184.04	170.06



Prices Subject To Change — We Always Ship At The Lowest Price In Effect

ALLIED ► 699