

HC-M-PN3-3,00-BU-V

Order No.: 1663556

The illustration shows versions, pneumatic male, female and female with valve

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1663556>



Pneumatics female connector with valve, for HC-M-PN3 module, cross section of hose 3.0 mm

Commercial data

GTIN (EAN)	 4 017918 123369
sales group	D044
Pack	10 pcs.
Customs tariff	85369010
Catalog page information	Page 463 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
10/31/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Electrical characteristics

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mechanical characteristics

Operating pressure, vacuum	6.00 bar
Internal diameter of pressure hose connection	3 mm
Insertion/withdrawal cycles	≥ 500

General characteristics

Color	black
-------	-------

Material data

Contact material	Delrin acetal
------------------	---------------

Certificates / Approvals



Certification

GOST, UL

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;