

Liquidtight Flexible Cord & Cable Fittings

T&B Catalog Number:



2534

78621002534

Status:

Active

Description:

3/4 in. straight die cast zinc liquidtight strain relief cord connector, cord range-.500-.625.

Application

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Meets Coast Guard CG293

General

Material	Die Cast Zinc
----------	---------------

Dimension Information

Hub Size (inches)	3/4
Dimension A (inches)	1 3/8
Dimension B (inches)	1 3/4
Dimension C (inches)	9/16
Cord Range (inches)	.500-.625
Throat Diameter (inches)	13/16

Specifications

3dmodel	Available on Website
---------	----------------------

Temperature Rating	105 C
--------------------	-------

Packaging

T&B Inner Pack	25
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	17.13 lbs. per 100

Application Support

Product Overview	Available on Website
------------------	----------------------

Specifications	Available on Website
----------------	----------------------

Portable Cord Selection Table	Available on Website
-------------------------------	----------------------

Notes

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

E 13938

For further technical assistance, please contact us...

8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com