

1300 SERIES

CRIMP TOOL

The 1300 Series Crimp tool is comprised of a universal tool frame and a comprehensive range of interchangeable dies. Designed for most popular interconnect applications this fully ratcheting tool utilises hardened dies for long life. A high impact storage case is available for the frame and selected dies.

Part No.	Crimp Size (mm)						Application
							
COAX							
2027					5.33	1.24	RG58, BNC, TNC, AMP
2028					6.30	1.24	RG59, 62AU, BNC, TNC, AMP
2034	6.50	5.41	1.73				RG58, 59, 62AU, BNC, TNC
2039	10.54		2.41				N Type for RG8, 11, 213, 216 cable.
2041	8.00	5.79	1.73				Cambridge CP88 and CP89
2042	8.78	8.00	6.50	1.07			F Type for RG6, 59 cable.
2046	5.41	4.52	1.73	1.07			RG58, 174, 50 and 75 ohm.
2047	8.00	6.40	1.73	2.00			RG59, 828, 50 and 75 ohm.
2050	10.21		2.39				RG8, BNC
2051	4.52	3.25	1.73				RG174
2075	8.25	5.46	1.65				RG58, 59, 62 teflon BNC, TNC.
2076	8.13	5.33	4.70				RG6, 58, BNC (Amphenol & Kings)
2084	10.90		2.54				N Type RG213 Amphenol
TERMINALS & SPLICES							
2029							14-26 AWG Terminal & Splices insulated
2031							14-22 AWG Terminal & Splices non-insulated
2033							14-22 AWG Open barrel non-insulated contacts
2035							14-22 AWG Terminal & Splices insulated
2040							14-22 AWG Terminal & Splices insulated max
FIBRE OPTIC							
2043	5.46	4.52	3.83				Universal fibre optic.
TELEPHONE PLUGS							
2061							RJ45 Stewart/WE type
2062							RJ11 Stewart/WE type
2063							Handset We type
2064							RJ45 AMP
2065							RJ11 AMP
2067							RJ11 DEC-MMJ AMP
2068							RJ45 10 position AT&T application

Part No.	Description
1302	1300 Tool Frame
9582.1920	1300 Storage Case