

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

REVISONS

DATE

DWN

APVD

8

OBSOLETE

6

7

5

64.01
[2.520]

66.04
[2.600]

24

25

7-103735-4

8

OBSOLETE

6

7

5

61.47
[2.420]

63.50
[2.500]

23

24

-7-103735-3

8

OBSOLETE

6

7

5

58.93
[2.320]

60.96
[2.400]

22

23

-7-103735-2

8

OBSOLETE

6

7

5

56.39
[2.220]

58.42
[2.300]

21

22

-7-103735-1

8

OBSOLETE

6

7

5

53.85
[2.120]

55.88
[2.200]

20

21

-7-103735-0

8

6

7

5

51.31
[2.020]

53.34
[2.100]

19

20

6-103735-9

8

OBSOLETE

6

7

5

48.77
[1.920]

50.80
[2.000]

18

19

-6-103735-8

8

OBSOLETE

6

7

5

46.23
[1.820]

48.26
[1.900]

17

18

-6-103735-7

8

6

7

5

43.69
[1.720]

45.72
[1.800]

16

17

6-103735-6

8

6

7

5

41.15
[1.620]

43.18
[1.700]

15

16

6-103735-5

8

6

7

5

38.61
[1.520]

40.64
[1.600]

14

15

6-103735-4

8

6

7

5

36.07
[1.420]

38.10
[1.500]

13

14

6-103735-3

8

OBSOLETE

6

7

5

33.53
[1.320]

35.56
[1.400]

12

13

-6-103735-2

8

6

7

5

30.99
[1.220]

33.02
[1.300]

11

12

6-103735-1

8

6

7

5

28.45
[1.120]

30.48
[1.200]

10

11

6-103735-0

8

6

7

5

25.91
[1.020]

27.94
[1.100]

9

10

5-103735-9

8

6

7

5

23.37
[.920]

25.40
[1.000]

8

9

5-103735-8

8

6

7

5

20.83
[.820]

22.86
[.900]

7

8

5-103735-7

8

6

7

5

18.29
[.720]

20.32
[.800]

6

7

5-103735-6

8

6

7

5

15.75
[.620]

17.78
[.700]

5

6

5-103735-5

8

6

7

5

13.21
[.520]

15.24
[.600]

4

5

5-103735-4

8

6

7

5

10.67
[.420]

12.70
[.500]

3

4

5-103735-3

8

6

7

5

8.13
[.320]

10.16
[.400]

2

3

5-103735-2

8

6

7

5

5.59
[.220]

7.62
[.300]

1

2

5-103735-1

REMARKS

PLATING

C

B

A

NO.
OF
POSN

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S. SHUEY
3-5-91

CHK
L. CASTAGNA
3-27-91

APVD
L. CASTAGNA
3-27-91

TE Connectivity

DIMENSIONS:
mm [INCHES]

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC

± -
± -
± -
± -
± -

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

ANGLES

± -
± -

MATERIAL

HOUSING: TYPED RESIN/NOT
THERMOPLASTIC
COLOUR: BLACK
CONTACTS: BRASS

FINISH

SEE TABLE

WEIGHT

—

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

PRODUCT SPEC

APPLICATION SPEC

—

NAME

HDR ASSY, VERT, SINGLE ROW
2.54[.100] Q, 0.64[.025] SQ POST,
WITH PLZN & LATCHING, AMPMODU MTE

SCALE

4:1

SHEET

2

OF

2

REV

U2

CUSTOMER DRAWING

00779

103735

4805 (3/11)