




SUNON

SPECIFICATION FOR APPROVAL

CUSTOMER :
DESCRIPTION : AXIAL AC FAN
DIMENSIONS : 92X92X25 mm
MODEL : SF11592A
P/N : 1092HBT
APPROVED NO :
APPROVED BY :
(AUTHORZIED)



DAWN.	 7/16	CHKD.	 7/17	APPD.		SPEC. NO.	292212300
						ISSUE DATE	07.12.1996
						EDITION	0
						REVISE DATE	
建準電機工業股份有限公司 SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD. 12FL., 120 CHUNG CHENG 1ST RD., TEL:886-7-7163069(41 LINES) KAOHSIUNG, TAIWAN, R. O. C. FAX:886-7-7163086~89							

AXIAL AC FAN
MODEL : SF11592A
P/N : 1092HBT



CHARACTERISTICS

1. Motor Design : Reliable Shaded-Pole Motor Construction.
2. Insulation Resistance : 500 Megohms minimum at 500 VDC.
3. Dielectric Strength : 1500 VAC for one minute.
4. Motor Protection : Impedence protected.
5. Noise Level : Measured in an semi-anechoic chamber
with background noise level below 15
dBA. The fan is running in free air with
microphone at a distance of one meter
from the fan intake.
6. Air Performance : Measured by a double chamber. The value are
recorded when the fan speed is stablized at
rated voltage.
7. Tolerances : $\pm 15\%$ on rated power and current.

建準電機工業股份有限公司 SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD.	SPEC. NO.	292212300	REVISE DATE	
	ISSUE DATE	07. 12. 1996	EDITION	0
	PAGE	2 OF 6		

SPECIFICATIONS

MODEL: SF11592A

P/N : 1092HBT

- 1-1. Rated Voltage : 115/115 VAC 50/60 HZ
- 1-2. Operating Voltage Range : 85-125 VAC
- 1-3. Starting Voltage : 85 VAC
- 1-4. Rated Speed : 2350/2850 RPM $\pm$ 5%
- 1-5. Air Delivery : 30/37 CFM
- 1-6. Static Pressure : 0.13/0.19 Inch-H₂O
- 1-7. Rated Current : 0.12/0.11 AMP
- 1-8. Input Power : 13/12 WATTS
- 1-9. Noise Level : 37/40 dB(A)
- 1-10. Direction of Rotation : Clockwies viewed from front face
- 1-11. Motor Protection : Impredance Protected
- 1-12. Operating Temperature : -10 to +70 Deg.C
- 1-13. Storage Temperature : -40 to +70 Deg.C
- 1-14. Bearing System : Precise ball bearing system
- 1-15. Weight : 280 g
- 1-16. Safety : UL/CSA Approvals



建準電機工業股份有限公司
SUNONWEALTH ELECTRIC
MACHINE INDUSTRY CO., LTD


SPEC. NO.	292212300	REVISE DATE	
ISSUE DATE	07. 12. 1996	EDITION	0
PAGE	3 OF 6		

SUNON

MODEL: SF11592A

P/N : 1092HBT

PERFORMANCE CURVES





建準電機工業股份有限公司 SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD.	SPEC. NO.	292212300	REVISE DATE	
	ISSUE DATE	07. 12. 1996	EDITION	0
	PAGE	4 OF 6		

MATERIAL**2. Material**

2-1 Frame : Thermoplastic PBT of UL 94V-0

2-2. Impeller : Thermoplastic PBT of UL 94V-0

2-3. Lead Wire : UL1007,24AWG

DIMENSIONS

UNIT : mm

建準電機工業股份有限公司 SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD.	SPEC. NO.	292212300	REVISE DATE	
	ISSUE DATE	07. 12. 1996	EDITION	0
	PAGE	5 OF 6		



SUNON

Notes

1. SUNON will not guarantee the products if the application of our products is exceeded the limitation which is specified on this specification.
2. In case of change of the specification specified on this document, a written notice is requested in advance.
3. Please do not touch the impeller with pressure and never bring the fan with lead wire. The bearings and lead wire may be damaged.
4. No guarantee on the products against the safety problem or failure caused by powder dust, drop of water or insect.
5. If there is any data or related documentation different from this data sheet, this data sheet is the principal reference.
6. For the purpose of MIS, please indicate SPEC No. on every order.
7. In case of the fan has no polarity protection function, wires with same color (electrode) must be connected together during the assembly. (i.e. red+red, black+black)

建準電機工業股份有限公司 SUNONWEALTH ELECTRIC MACHINE INDUSTRY CO., LTD.	SPEC. NO.	292212300	REVISE DATE	
	ISSUE DATE	07. 12. 1996	EDITION	0
	PAGE	6 OF 6		