

D

C

B

A


D

C


B

A

- THIS RECEPTACLE WILL MATE WITH ANY 5C5, SIZE 3 PLUG IN AMPLIMITE SERIES.
- USE (5) POWER 8, OR COAX SOCKET CONTACTS. CONSULT PRODUCT ENGINEERING FOR MORE DETAILS.
- CADMIUM PER QQ-P-416.
- FINISH: TIN PER ASTM-B-545 .000200 MIN THK OVER COPPER PER AMS2418 .000100-.000200 THK.
- ALL EXCEPT FOR 212059-5 AND 212059-6.
- 4-40 UNC-3B CLINCH NUT, 2 REQ'D.
- CUSTOMER PART NO. INK STAMPED FAR SIDE.
- UL/CSA DESIGNATION STAMPED IN THIS AREA, OPTIONAL.
- STEEL PER ASTM-A-109.
- BRASS PER ASTM-B-36.
- GOLD PLATED PER MIL-G-45204 OVER COPPER PER AMS2418.
- FINISH: TIN PER ASTM-B-545 .000400 MIN THK OVER COPPER PER AMS2418 .000050 MIN THK.
- ZINC PLATE PER ASTM-B-633, .000200-.000400 THK WITH SUPPLEMENTARY CHROMATE (Cr3+)



CLINCH NUT #4-40UNC
2 REQ'D
MAT'L: CARBON STEEL
FINISH: PLATED ZINC
YELLOW CHROMATE
212059-5 ONLY



-	56912	5-212059-5
-	913	5-212059-1
B010942-0008	71011	1-212059-3
B010942-0007	71011	1-212059-1
-	912	1-212059-0
-	912	212059-9
-	-	212059-8
B010942-0016	71011	212059-7
311P405-10S-B-15	71011	212059-6
-	4569	212059-5
97942-645A935H01	379	212059-4
-	49	212059-3
311P405-10S-B-12	71011	212059-2
-	39	212059-1
CUSTOMER PART NO	REMARKS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± - ± 0°30'
ANGLES
FINISH

DWN
T. SHUEY
14JAN88

CHK
A. EMADI
26JAN88

NAME
A. EMADI
26JAN88

PRODUCT SPEC

APPLICATION SPEC

SIZE
A1

CAGE CODE
00779

DRAWING NO
212059

RESTRICTED TO

TE Connectivity

RECEPTACLE ASSEMBLY
AMPLIMITE 5C5
SERIES 109, SIZE 3, COAX MIX

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
AK