

DUBBELTRYCKE + STOPPKNAPP

Partnumber: ZB4BA711147

Wholesalernumber: 3733067

EAN 13 code: 3389119044103

white flush/red projecting/white flush triple-headed pushbutton Ø22 with marking

Technical information

► Functional

type of operator	spring return
operator profile	2 flush - 1 central projecting STOP pushbuttons
operators description	white "up arrow" - white "down arrow" - red "STOP"
operator profile	red projecting, white STOP
	white flush, black down arrow
	white flush, black up arrow
electrical composition code	C1 for <= 9 contacts using single blocks in front mounting
	C2 for <= 9 contacts using single and double blocks in front mounting
	C11 for <= 3 contacts using single blocks in front mounting

► Performance

mechanical durability	1000000 cycles cycles
-----------------------	-----------------------

► Product identification

range of product	Harmony XB4
product or component type	head for triple-headed pushbutton
device short name	ZB4
bezel material	black metal
mounting diameter	22 mm mm
colour of marking	black marking when white caps
	white marking when green, red or black caps

► Additional information

sale per indivisible quantity	1
-------------------------------	---

► Physical characteristics

product weight	0.056 kg kg
resistance to high pressure washer	7000000 Pa at 55 °C,distance: 0.1 m
shape of signaling unit head	rectangular

► Environment

ambient air temperature for storage	-40...70 °C °C
ambient air temperature for operation	-25...70 °C °C
class of protection against electric shock	class I conforming to IEC 60536
IP degree of protection	IP66 conforming to IEC 60529
	IP69K conforming to IEC 60529
NEMA degree of protection	NEMA 13
	NEMA 4X
IK degree of protection	IK03 conforming to IEC 50102
vibration resistance	5 gn (f = 2...500 Hz) conforming to IEC 60068-2-6
	30 gn for 18 ms half sine wave acceleration conforming to IEC 60068-2-27
shock resistance	50 gn for 11 ms half sine wave acceleration conforming to IEC 60068-2-27

► Certifications and standards

standards	CSA C22-2 No 14
	EN/IEC 60947-1
	EN/IEC 60947-5-1
	EN/IEC 60947-5-4
	EN/IEC 60947-5-5
	JIS C 4520
	UL 508

product certifications

BV
CSA
DNV
GL
LROS (Lloyds register of shipping)
RINA
UL listed

Supplier information

Supplier: Schneider Electric Sverige AB

Fax: +46 155 26 54 91

Web: <http://www.schneider-electric.se>

Adress: Eskilstunavägen 7, 611 56 Nyköping

Phone: +46 155 26 54 00

e-Mail: info@se.schneider-electric.com