

HELLERMANN TYTON IDENTIFICATION ENGINEERED PRODUCTS SECTION

HellermannTyton provides a wide variety of identification products, as reflected in the previous pages. HellermannTyton's products meet the needs of almost any application; however, there may be need to specify products to European standards or to highly specialized applications.

The Engineering Product Section is a tool for finding identification products manufactured by the HellermannTyton companies worldwide. These products are **not stocked as standard products, but can be ordered to specifications with a short lead time**. Pricing on any product can be obtained by contacting your HellermannTyton representative or directly at (800) 537-1512 or email: corp@htamericas.com. Minimum purchase quantities may apply.

SS, S, K & G Expandable Sleeve Tools

Expandable sleeve tools can be used with all products specified in the engineering section.

SS, S, K & G Expandable Sleeve Tools

Part No.	Description	Inner Diameter		Max. Sleeve Length	Max. Tool Expansion	Global Part No.
		Min.	Max.			
TYPES	3 Prong Tool	.047" (1.20mm)	.078" (2.0mm)	.787" (20mm)	.590" (15.0mm)	623-21220 prongs are fixed to this size only
TYPES	3 Prong Tool (2.50mm)	.098" (4.0mm)	.157" (4.0mm)	.787" (20mm)	.590" (15.0mm)	623-22540 prongs are fixed
TYPEK	3 Prong Tool (5.0mm)	.196" (5.0mm)	.393" (10.0mm)	.787" (32mm)	1.25" (17.0mm)	623-25010 prongs are fixed
TYPEG	3 Prong Tool (10.0mm)	.393" (25.0mm)	1.00" (25.0mm)	1.96" (50mm)	1.10" (28.0mm)	623-21025 prongs are fixed




Photo shows the complete DKit. Blue tool body is the same for TYPES, TYPESS and TYPEK.

Lubricant

Grade M exhibits a restricted rate of drying and is guaranteed to be completely fungistic, which is very important where electrical equipment is intended for use under tropical conditions. AFS 611A

Global Part Number User Key


The chart below can help you determine the global part number for any of the items on the next several pages. However, also please use the HellermannTyton part number to order products.

Tool Kit

Part No.	Global Part No.	Description	Sleeve Lengths
DKit	623-10000	The complete tool kit*	
SFT3032*	623-10001	Replacement tool body	Fits all replacement prongs
SFT3033*	623-11230	Replacement prongs .047" to .118" (1.2mm to 3.0mm)	.787" (20mm)
SFT3034*	623-13050	Replacement prongs .118" to .216" (3.0mm to 5.5mm)	.787" (20mm)
SFT3035*	623-15511	Replacement prongs .216" to .452" (5.5mm to 11.5mm)	1.18" (30mm)
SFT3030B SFT3040*	623-11230	Replacement locator	Prong Locator*
LUBM284ML LUBM2DR LUBM5L	284ml bottle 2 dram bottle* 5 liter container		

*Included in DKit

Global Part Number User Key



Legend	A	B	C	D	E	F	G	H	I	J	K	L	M	N	O	P	Q	R	S	T	U	V	W	X	Y	Z
Legend No.	01	02	03	04	05	06	07	08	09	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26

Legend	0	1	2	3	4	5	6	7	8	9	+	-	/	.	±	unbedr.	<	>	;	&	=	,
Legend No.	60	61	62	63	64	65	66	67	68	69	70	71	72	31	73	75	76	77	78	79	80	81

Color	Code
Black (BK)	0 Black
Brown (BN)	1 Brown
Red (RD)	2 Red
Orange (OG)	3 Orange
Yellow (YE)	4 Yellow
Green (GN)	5 Green
Blue (BU)	6 Blue
Violet (VT)	7 Violet
Gray (GY)	8 Gray
White (WH)	9 White