

## TECHNICAL SPECIFICATIONS

### Materials:

**Unshielded Hood:** Polyamid - UL-recognised

**Operating Temperature:** -55°C to +110°C

**Thumbscrews:** UNC 4-40 (Standard)

**Shielded Hood:** ABS/PC - UL-recognised


**Plating:** Nickel over Copper

**Operating Temperature:** -55°C to +110°C


**Thumbscrews:** UNC 4-40 (Standard)



MHDAPK 15



MHDAPK 25



### Ordering information:

Unshielded Version

| Size:  | P/N - Kitted: | Product Code: |
|--------|---------------|---------------|
| 15-way | 6211-0100-32  | DAPK15-JS     |
| 25-way | 6211-0100-33  | DAPK25-JS     |

### Ordering information:

Shielded Version

| Size:  | P/N - Kitted: | Product Code: |
|--------|---------------|---------------|
| 15-way | 6211-0100-42  | DAPK15-JS/MET |
| 25-way | 6211-0100-43  | DAPK25-JS/MET |

### Note:

All adapters are delivered with 2 long jackscrews in standard versions as seen in above drawings and ordering information.