

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .



COPYRIGHT

-

BY TYCO ELECTRONICS CORPORATION.

ALL INTERNATIONAL RIGHTS RESERVED.

LOC

G

DIST

14

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD


E1

REV PER ECR 09-015243

29JUL09

JR

TM

AMP
WIRE RANGEE13288
Listed1/0 AWG
SOLID OR STRANDED1/0 AWG
STRANDEDLR7189
CertifiedMILITARY P/N
AND CLASS1/0 AWG
SOLID OR STRANDEDMS 20659-152
CLASS 2TIN PL 0.00254[.000100] MIN THK
PER ASTM B-545COPPER ASTM B-152
1.78±0.08 [.070±.003]
ANNEALED

36918


FINISH

MATERIAL

PART NO.

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAXVOLTAGE RATING:
N/ACIRCULAR MIL AREA:
42.4-60.6mm² [83,700-119,500]

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM [INCHES]MATERIAL
SEE TABLETOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± 0.20[.008]
3 PLC ± -
4 PLC ± -
ANGLES ± -FINISH
SEE TABLEDWN
DK SCHRUM

7/2/91

CHK
RD HEIM

8/15/91

APVD
AJ KAUFMAN

8/16/91

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME

TERMINAL, RING TONGUE,
SOLISTRAND,
WIRE SIZE: 50.0mm² [1/0] AWG

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-36918

CUSTOMER DRAWING

SCALE 2:1

SHEET 1 OF 1

REV E1