

**FAST, COMPACT, AFFORDABLE
IT'S ALL HERE IN BLACK & WHITE**



HL-2200 SERIES
COMPACT MONO LASER PRINTERS



FAST, VERSATILE AND SIMPLE

There are times when high speed, high quality, low cost black and white printing is precisely what is needed. Among the fastest in their class, our HL-2200 series of compact mono laser printers deliver precisely that.

HL-2270DW COMPACT MONO LASER PRINTER



YOU'RE COVERED

Buy a Brother printer and our UK-based team of specialists is always there to help, advise and support. Whatever you need to know, whenever you need it, online, on the phone or by email.



INCREASE EFFICIENCY

Fast printing speeds up the way you work
– at home or in the office



SAVE ON PAPER COSTS

Slash your paper costs with double-sided printing



LESS TIME REFILLING

Extra tray capacity for larger documents
and longer print runs



LOWER RUNNING COSTS

High yield toner option lets you save even more



MORE THAN A4

For those one-off jobs, envelopes, labels,
compliment slips



UP TO SPEED

The first print is ready in next to no time



SHARE WITH UP TO 3 PEOPLE

Give all your team the benefits of one versatile printer

GREEN AND CLEAN



-  Reduce costs with low energy usage
-  Save power with a deep sleep mode from as low as 0.8w and a TEC value from 0.913kWh/week

-  Save up to 75% on your paper usage with the booklet print feature
-  Reduce the need for reprint by using Brother original supplies

IT'S EASY TO CHOOSE THE RIGHT ONE

	 HL-2130	 HL-2240	 HL-2240D	 HL-2250DN	 HL-2270DW
Print speed	20ppm	24ppm	24ppm	26ppm	26ppm
First print out	Under 10 seconds	Under 8.5 seconds	Under 8.5 seconds	Under 8.5 seconds	Under 8.5 seconds
Automatic double-sided print			✓	✓	✓
Network ready				✓	✓
Wireless network ready					✓
Paper capacity (standard / manual feed)	250 / 1	250 / 1	250 / 1	250 / 1	250 / 1
In the box toner	700 pages	700 pages	700 pages	700 pages	1200 pages
TN-2010 toner cartridge (1000 pages†)	✓				
TN-2210 toner cartridge (1200 pages†)		✓	✓	✓	✓
TN-2220 toner cartridge (2600 pages†)		✓	✓	✓	✓
DR-2200 drum unit (12,000 pages†)	✓	✓	✓	✓	✓

BROTHER ORIGINALS GET THE BEST OUT OF YOUR BROTHER

Using Brother original supplies in your Brother printer guarantees you optimum performance and great value for money. If you want Brother quality print-outs – it has to be Brother originals inside.

TN2210 / TN2220 / TN2010 / DR2200

† Declared yield in accordance with ISO/IEC 19752

YOUR CHOICE OF BLACK AND WHITE PRINTERS

Wherever you're printing, at home or in the office, with its versatility, economy and quality, a Brother HL-2200 series mono laser printer will really work for you.

IDEAL FOR YOUR HOME

Being so compact, wherever you place your choice of Brother 2200 printer in the home, it'll fit right in – especially with the freedom wireless connection gives – and, with low running costs it sits well within your budget too.

PERFECT FOR THE OFFICE

Home office, small or growing business; the compact HL-2200 series lets you take full advantage of some very professional features – and benefits.

There's the high yield toner option that prints an impressive 2600 pages, to keep your running costs low, while the double-sided and booklet printing options help save money and paper. Features and savings that can be shared among three users, thanks to their networking capabilities.

Looking for a black and white laser printer for home or the office?
The choice is easy – the Brother HL-2200 series.



AT HOME OR IN THE OFFICE, BLACK AND WHITE PRINTERS THAT WORK HARD FOR YOU

Bank statements, spreadsheets, orders, invoices, reports, tenders, web pages, emails...

Whether you're operating out of your home or a small office, and whatever your business documents may be, you can have them printed out and in your hand quickly, sharply and economically with any one of the five black and white laser printers in our Brother HL-2200 series.

Combine this with all the other outstanding features such as the freedom of a wireless connection, the option of a high yield toner cartridge and a generous paper tray, and there's bound to be one in the range that's right for you.

Big on performance, compact in size and remarkably low cost to run, if you need a mono printer, the choice is as clear as black and white: a Brother HL-2200 series.

**PERFECT
FOR**



- ☒ **Growing businesses – at home, start-up or small office**
- ☒ **Anywhere that space is at a premium**
- ☒ **Sharing with up to 3 users – with its easy networking facility**
- ☒ **Double-sided printing to save paper**
- ☒ **Saving money with low operating costs**

Technical Specifications	HL-2130	HL-2240	HL-2240D	HL-2250DN	HL-2270DW
Print speed	20ppm	24ppm	24ppm	26ppm	26ppm
First print out	Under 10 seconds	Under 8.5 seconds	Under 8.5 seconds	Under 8.5 seconds	Under 8.5 seconds
Emulation	GDI	GDI	GDI	PCL6	PCL6
Print resolution	2400 x 600dpi	2400 x 600dpi	2400 x 600dpi	2400 x 600dpi	2400 x 600dpi
Memory	8MB	8MB	8MB	32MB	32MB
Automatic double-sided print			Yes	Yes	Yes
Hi-speed USB 2.0 interface	Yes	Yes	Yes	Yes	Yes
Network ready				Yes	Yes
Wireless network ready					Yes
Paper capacity (standard / manual feed)	250 / 1	250 / 1	250 / 1	250 / 1	250 / 1
One sheet manual feed tray	Yes	Yes	Yes	Yes	Yes
Maximum media size	216/406.4mm	216/406.4mm	216/406.4mm	216/406.4mm	216/406.4mm
Maximum media weight	163g/m2	163g/m2	163g/m2	163g/m2	163g/m2
In the box toner	700 pages	700 pages	700 pages	700 pages	1200 pages
Dimensions (without carton) W x D x H	368x330x183mm	368x360x183mm	368x360x183mm	368x360x183mm	368x360x183mm
Weight (without carton)	6.7kg	6.7kg	7.0kg	7.0kg	7.0kg
Noise level (operating)	Approx 53dB(A)	Approx 53dB(A)	Approx 53dB(A)	Approx 53dB(A)	Approx 53dB(A)
Power consumption (deep sleep / ready / operating)	0.8/62/421W	0.9/65/495W	0.9/65/495W	0.9/65/495W	0.9/65/495W
TEC value	0.913kWh/Week	1.137kWh/Week	1.137kWh/Week	1.305kWh/Week	1.342kWh/Week
TN-2010 toner cartridge (1000 pages†)	Yes				
TN-2210 toner cartridge (1200 pages†)		Yes	Yes	Yes	Yes
TN-2220 toner cartridge (2600 pages†)		Yes	Yes	Yes	Yes
DR-2200 drum unit (12,000 pages†)	Yes	Yes	Yes	Yes	Yes

† Declared yield in accordance with ISO/IEC 19752



Please visit www.brother.co.uk for full specifications.
All specifications are subject to change.

For iPhone / Android users scan this QR code for further information on the range.

Contact:



brother
at your side



coo!earth

Brother UK Ltd, Audenshaw, Manchester M34 5JD
Tel: +44(0)8444 999 444 **Fax:** +44(0)161 931 2218
Web: www.brother.co.uk

4935 2200 SERIES RANGE RAPPORT 04/11 V1

All specifications correct at time of printing. Brother is a registered trademark of Brother Industries Ltd. Brand product names are registered trademarks or trademarks of their respective companies.

Material code ZLFTHL2200SERIESU1