



#### FEATURES:

- ✓ Ideal for providing a jumper on pin jack test boxes or panels.
- ✓ Mates with Pomona Model 4543 or any other standard .080" pin jack.

#### MATERIALS:

##### Upper Connector (Double Pin Tip Jack):

Material: Jack body – Brass per QQ-B-626, Alloy 360, 1/2/ Hard.

Spring: Beryllium Copper per QQ-C-533, Alloy 172, Cond. H.T.

Finish: Gold plated per MIL-G-45204, Type II, Class 00 over electroless nickel per MIL-C-26074, Class 1, 200/300 micro-inches.

##### Lower Connector (Double Pin Tip Plug):

Material: Body – Brass per QQ-B-626, Alloy 360, 1/2/ Hard.

Finish: Gold plated per MIL-G-45204, Type II, Class 00 over electroless nickel per MIL-C-26074,

Insulation: ABS molded to Pin Jacks and bodies.

#### RATINGS:

Operating Voltage: Hands free usage in controlled voltage environments: 3000 Vrms maximum. For CE compliance: not intended for hand-held use at voltages above 33 Vrms/70 Vdc.

Current: 5 Amps

Operating Temperature: +122°F (+50°C) Max.

#### ORDERING INFORMATION: Model 3452-Color

Color =: 0 (Black), 2 (Red)

Ordering Example: 3452-2 (red)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Sales: 800-490-2361 Fax: 888-403-3360 Technical Support: 800-241-2060 (technicalsupport@pomonatest.com)

For "Where to Buy" information, visit the Pomona web site at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)