

**IQP3QPQPR4-A****InstaPATCH® QUATTRO MC Male to MC Male Category 6 U/UTP Ribbon Trunk Cable, 4-port, plenum, blue**

## Dimensions

Cord Length, maximum	90 m   295 ft
Cord Length, minimum	3 m   10 ft

## Electrical Specifications

ANSI/TIA Category	6
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	1000 V

## Environmental Specifications

Environmental Space	Plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL   ETL

## General Specifications

Construction Type	Ribbon
Interface, connector A	MC Male
Interface, connector B	MC Male
Brand	InstaPATCH® QUATTRO
Cable Type	U/UTP (unshielded)
Information Outlet Color	Silver
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Jacket Color	Blue
Package Quantity	1
Pairs, quantity	16
Total Ports, quantity	4

## Mechanical Specifications

Conductor Type	Solid
Material Type	Copper alloy   Polycarbonate   Zinc
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, connector A, minimum	100 times
Plug Insertion Life, connector B, minimum	100 times
Plug Retention Force, minimum	133 N   30 lbf

# Product Specifications

COMMSCOPE®

IQP3QPQPR4-A

Wiring

T568B

POWERED BY

SYSTIMAX®

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU  
ISO 9001:2008

**Classification**  
Compliant  
Designed, manufactured and/or distributed under this quality management system

