




13			12		11		10		9		8		7		6		5		4		3		2		1															
J	PACKAGING SEE NOTE 4 SHT 1		4-6 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		BULK															
			8-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TUBES															
	DIM. M±0.25 MM				6.10 (.240)				6.10 (.240)				6.10 (.240)				6.10 (.240)								8.13 (.320)		8.13 (.320)													
	PLATING				150 TIN				15 GOLD				30 GOLD												15 GOLD		30 GOLD													
I	DIM. H				2.54 (.100)				2.54 (.100)				2.54 (.100)												4.57 (.180)		4.57 (.180)													
H	CKTS	DIM. A		DIM. B		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS													
		MM	IN	MM	IN																																			
G	04	5.08	.200	2.54	.100	015-91-2040	015-91-6040	N/A	015-91-0040	015-91-6042	N/A	015-91-3040	015-91-6043	N/A	015-91-0048	015-91-5049	04	H	06	7.62	.300	5.08	.200	015-91-2060	015-91-6060	N/A	015-91-0060	015-91-6062	N/A	015-91-0068	015-91-5069	06								
	08	10.16	.400	7.62	.300	015-91-2080	015-91-6080	015-91-3087	015-91-0080	015-91-6082	015-91-3086	015-91-3080	015-91-6083	015-91-3088	015-91-0088	015-91-5089	08		10	12.70	.500	10.16	.400	015-91-2100	015-91-6100	015-91-3107	015-91-0100	015-91-6102	015-91-3106	015-91-3100	015-91-6103	015-91-3108	015-91-0108	015-91-5109	10					
F	12	15.24	.600	12.70	.500	015-91-2120	015-91-6120	015-91-3127	015-91-0120	015-91-6122	015-91-3126	015-91-3120	015-91-6123	015-91-3128	015-91-0128	015-91-5129	12	E	14	17.78	.700	15.24	.600	015-91-2140	015-91-6140	015-91-3147	015-91-0140	015-91-6142	015-91-3146	015-91-3140	015-91-6143	015-91-3148	015-91-0148	015-91-5149	14					
	16	20.32	.800	17.78	.700	015-91-2160	015-91-6160	015-91-3167	015-91-0160	015-91-6162	015-91-3166	015-91-3160	015-91-6163	015-91-3168	015-91-0168	015-91-5169	16		18	22.86	.900	20.32	.800	015-91-2180		015-91-3187	015-91-0180	015-91-3186	015-91-3180	015-91-3188	015-91-0188	015-91-5189	18							
D	20	25.40	1.000	22.86	.900	015-91-2200	015-91-6200	015-91-3207	015-91-0200	015-91-6202	015-91-3206	015-91-3200	015-91-6203	015-91-3208	015-91-0208	015-91-5209	20	C	22	27.94	1.100	25.40	1.000	015-91-2220		015-91-3227	015-91-0220	015-91-3226	015-91-3220	015-91-3228	015-91-0228	015-91-5229	22							
	24	30.48	1.200	27.94	1.100	015-91-2240		015-91-3247	015-91-0240		015-91-3246	015-91-3240		015-91-3248	015-91-0248	015-91-5249	24		26	33.02	1.300	30.48	1.200	015-91-2260	015-91-6260	015-91-3267	015-91-0260	015-91-6262	015-91-3266	015-91-3260	015-91-3268	015-91-0268	015-91-5269	26						
C	28	35.56	1.400	33.02	1.300	015-91-2280		015-91-3287	015-91-0280		015-91-3286	015-91-3280		015-91-3288	015-91-0288	015-91-5289	28	B	30	38.10	1.500	35.56	1.400	015-91-2300		015-91-3307	015-91-0300	015-91-3306	015-91-3300	015-91-3308	015-91-0308	015-91-5309	30							
	32	40.64	1.600	38.10	1.500	015-91-2320		015-91-3327	015-91-0320		015-91-3326	015-91-3320		015-91-3328	015-91-0328	015-91-5329	32		34	43.18	1.700	40.64	1.600	015-91-2340		015-91-3347	015-91-0340	015-91-3346	015-91-3340	015-91-3348	015-91-0348	015-91-5349	34							
B	36	45.72	1.800	43.18	1.700	015-91-2360		015-91-3367	015-91-0360		015-91-3366	015-91-3360		015-91-3368	015-91-0368	015-91-5369	36	A	38	48.26	1.900	45.72	1.800	015-91-2380		015-91-3387	015-91-0380	015-91-3386	015-91-3380	015-91-3388	015-91-0388	015-91-5389	38							
	40	50.80	2.000	48.26	1.900	015-91-2400	015-91-6400	015-91-3407	015-91-0400	015-91-6402	015-91-3406	015-91-3400	015-91-6403	015-91-3408	015-91-0408	015-91-5409	40		42	53.34	2.100	50.80	2.000	015-91-2420		015-91-3427	015-91-0420	015-91-3426	015-91-3420	015-91-3428	015-91-0428	015-91-5429	42							
A	44	55.88	2.200	53.34	2.100	015-91-2440		015-91-3447	015-91-0440		015-91-3446	015-91-3440		015-91-3448	015-91-0448	015-91-5449	44	Z	46	58.42	2.300	55.88	2.200	015-91-2460		015-91-3467	015-91-0460	015-91-3466	015-91-3460	015-91-3468	015-91-0468	015-91-5469	46							
	48	60.96	2.400	58.42	2.300	015-91-2480		015-91-3487	015-91-0480		015-91-3486	015-91-3480		015-91-3488	015-91-0488	015-91-5489	48		50	63.50	2.500	60.96	2.400	015-91-2500	015-91-6500	015-91-3507	015-91-0500	015-91-6502	015-91-3506	015-91-3500	015-91-6503	015-91-3508	015-91-0508	015-91-5509	50					
Z	52	66.04	2.600	63.50	2.500	015-91-2520		015-91-3527	015-91-0520		015-91-3526	015-91-3520		015-91-3528	015-91-0528	015-91-5529	52	Y	54	68.58	2.700	66.04	2.600	015-91-2540		015-91-3547	015-91-0540	015-91-3546	015-91-3540	015-91-3548	015-91-0548	015-91-5549	54							
	56	71.12	2.800	68.58	2.700	015-91-2560		015-91-3567	015-91-0560		015-91-3566	015-91-3560		015-91-3568	015-91-0568	015-91-5569	56		58	73.66	2.900	71.12	2.800	015-91-2580		015-91-3587	015-91-0580	015-91-3586	015-91-3580	015-91-3588	015-91-0588	015-91-5589	58							
Y	60	76.20	3.000	73.66	2.900	015-91-2600		015-91-3607	015-91-0600		015-91-3606	015-91-3600		015-91-3608	015-91-0608	015-91-5609	60	X	62	78.74	3.100	76.20	3.000	015-91-2620		015-91-3627	015-91-0620	015-91-3626	015-91-3620	015-91-3628	015-91-0628	015-91-5629	62							
	64	81.28	3.200	78.74	3.100	015-91-2640		015-91-3647	015-91-0640		015-91-3646	015-91-3640		015-91-3648	015-91-0648	015-91-5649	64		66	83.82	3.300	81.28	3.200	015-91-2660		015-91-3667	015-91-0660	015-91-3666	015-91-3660	015-91-3668	015-91-0668	015-91-5669	66							
X	68	86.36	3.400	83.82	3.300	015-91-2680		015-91-3687	015-91-0680		015-91-3686	015-91-3680		015-91-3688	015-91-0688	015-91-5689	68	W	70	88.90	3.500	86.36	3.400	015-91-2700		015-91-3707	015-91-0700	015-91-3706	015-91-3700	015-91-3708	015-91-0708	015-91-5709	70							
	72	91.44	3.600	88.90	3.500	015-91-2720		015-91-3727	015-91-0720		015-91-3726	015-91-3720		015-91-3728	015-91-0728	015-91-5729	72		74	93.98	3.700	91.44	3.600	015-91-2740		015-91-3747	015-91-0740	015-91-3746	015-91-3740	015-91-3748	015-91-0748	015-91-5749	74							
W	76	96.52	3.800	93.98	3.700	015-91-2760		015-91-3767	015-91-0760		015-91-3766	015-91-3760		015-91-3768	015-91-0768	015-91-5769	76	V	78	99.06	3.900	96.52	3.800	015-91-2780		015-91-3787	015-91-0780	015-91-3786	015-91-3780	015-91-3788	015-91-0788	015-91-5789	78							
	80	101.60	4.000	99.06	3.900	015-91-2800		015-91-3807	015-91-0800		015-91-3806	015-91-3800		015-91-3808	015-91-0808	015-91-5809	80		82	104.14	4.100	101.60	4.000	71308-0082		71308-0482	71308-0182	71308-0582	71308-0282	71308-0682	71308-1182	71308-1282	82							
V	84	106.68	4.200	104.14	4.100	71308-0084		71308-0484	71308-0184		71308-0584	71308-0284		71308-0684	71308-1184	71308-1284</																								

13		12		11				10		9		8		7		6		5		4		3		2		1	
J		IN TAPE AND REEL WITH SHALLOW POCKET TAPE												BULK / IN TUBES										J			
		PACKAGING SEE NOTE 4. SHT 1		4-8 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS										BULK		BULK							
				10-100 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS										TUBES		TUBES							
		DIM. M±0.25 MM				6.10 (.240)		6.10 (.240)										8.13 (.320)		13.59 (.535)							
		PLATING				30 GOLD		15 GOLD										150 TIN		150 TIN							
		DIM. H				2.54 (.100)		2.54 (.100)										4.57 (.180)		4.57 (.180)							
I		CKTS		DIM. A		DIM. B		EDP NUMBER		EDP NUMBER								EDP NUMBER		EDP NUMBER		CKTS					
				MM	IN	MM	IN																				
		04	5.08	.200	2.54	.100																	04				
		06	7.62	.300	5.08	.200			015-91-6068														06				
		08	10.16	.400	7.62	.300			015-91-6088														08				
		10	12.70	.500	10.16	.400			015-91-6108										713088010		71308-8210		10				
		12	15.24	.600	12.70	.500																	12				
H		14	17.78	.700	15.24	.600	015-91-6148																14				
		16	20.32	.800	17.78	.700													713088016				16				
		18	22.86	.900	20.32	.800																	18				
		20	25.40	1.000	22.86	.900																	20				
		22	27.94	1.100	25.40	1.000																	22				
		24	30.48	1.200	27.94	1.100																	24				
		26	33.02	1.300	30.48	1.200																	26				
		28	35.56	1.400	33.02	1.300																	28				
G		30	38.10	1.500	35.56	1.400																	30				
		32	40.64	1.600	38.10	1.500																	32				
		34	43.18	1.700	40.64	1.600																	34				
		36	45.72	1.800	43.18	1.700																	36				
		38	48.26	1.900	45.72	1.800																	38				
		40	50.80	2.000	48.26	1.900																	40				
		42	53.34	2.100	50.80	2.000																	42				
F		44	55.88	2.200	53.34	2.100																	44				
		46	58.42	2.300	55.88	2.200																	46				
		48	60.96	2.400	58.42	2.300																	48				
		50	63.50	2.500	60.96	2.400																	50				
		52	66.04	2.600	63.50	2.500																	52				
		54	68.58	2.700	66.04	2.600																	54				
		56	71.12	2.800	68.58	2.700																	56				
E		58	73.66	2.900	71.12	2.800																	58				
		60	76.20	3.000	73.66	2.900																	60				
		62	78.74	3.100	76.20	3.000																	62				
		64	81.28	3.200	78.74	3.100																	64				
		66	83.82	3.300	81.28	3.200																	66				
		68	86.36	3.400	83.82	3.300																	68				
		70	88.90	3.500	86.36	3.400																	70				
		72	91.44	3.600	88.90	3.500																	72				
D		74	93.98	3.700	91.44	3.600																	74				
		76	96.52	3.800	93.98	3.700																	76				
		78	99.06	3.900	96.52	3.800																	78				
		80	101.60	4.000	99.06	3.900																	80				
		82	104.14	4.100	101.60	4.000																	82				
		84	106.68	4.200	104.14	4.100																	84				
		86	109.22	4.300	106.68	4.200																	86				
C		88	111.76	4.400	109.22	4.300																	88				
		90	114.30	4.500	111.76	4.400																	90				
		92	116.84	4.600	114.30	4.500																	92				
		94	119.38	4.700	116.84	4.600																	94				
		96	121.92	4.800	119.38	4.700																	96				
		98	124.46	4.900	121.92	4.800																	98				
		100	127.00	5.000	124.46	4.900																	100				
B		NO PEG VERSION										SEE SHEET 1 EC NO: UCP2014-0809 DRAWN:KIPPER 2013/08/20 CHKD:JBELL 2013/08/20 APPR:FSMITH 2013/09/03		QUALITY SYMBOLS ▽=0 ▽/▽=0 ▽/▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE		DESIGN UNITS INCH		THIRD ANGLE PROJECTION			
																mm		INCH		DRAWN BY KMS		DATE 1999/10/15				TITLE SALES ASSY INSULATOR DUAL ROW SMT W/BREAK-OFF .025SQ PIN GULLWING .100	
A		(ALSO SEE SHEET 2)										K5		REV		ANGULAR ±1/2°		MATERIAL NO.		DOCUMENT NO.		SHEET NO.					
																DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-71308-001		3 OF 6					
		ib_frame_C_P_AM.T Rev. G 2012/01/11																									

13		12		11		10		9		8		7		6		5		4		3		2		1			
J		PACKAGING SEE NOTE 4 SHT 1				4-8 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		BULK		BULK			
						10-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TUBES		TUBES			
		DIM. M±0.25 MM				6.10 (.240)		6.10 (.240)		6.10 (.240)		6.10 (.240)		6.10 (.240)		8.13 (.320)		8.13 (.320)		8.13 (.320)							
		PLATING				150 TIN		15 GOLD		30 GOLD		150 TIN		15 GOLD		30 GOLD											
		DIM. H				2.54 (.100)		2.54 (.100)		2.54 (.100)		4.57 (.180)		4.57 (.180)		4.57 (.180)											
I	CKTS	DIM. A		DIM. B		DIM. C		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS		
		MM	IN	MM	IN	MM	IN																				
04	5.08	.200	2.54	.100	----	----		015-91-1041	015-91-6044	015-91-1042	015-91-6045	015-91-1043	015-91-6046	015-91-1044	015-91-0047	015-91-1040									04		
06	7.62	.300	5.08	.200	2.54	.100		015-91-1061	015-91-6064	015-91-1062	015-91-6065	015-91-1063	015-91-6066	015-91-1064	015-91-0067	015-91-1060									06		
08	10.16	.400	7.62	.300	5.08	.200		015-91-1081	015-91-6084	015-91-1082	015-91-6085	015-91-1083	015-91-6086	015-91-1084	015-91-0087	015-91-1080									08		
10	12.70	.500	10.16	.400	7.62	.300		015-91-1101	015-91-6104	015-91-1102	015-91-6105	015-91-1103	015-91-6106	015-91-1104	015-91-0107	015-91-1100									10		
12	15.24	.600	12.70	.500	10.16	.400		015-91-1121		015-91-1122		015-91-1123		015-91-1124	015-91-0127	015-91-1120									12		
14	17.78	.700	15.24	.600	12.70	.500		015-91-1141	015-91-6144	015-91-1142	015-91-6145	015-91-1143	015-91-6146	015-91-1144	015-91-0147	015-91-1140									14		
16	20.32	.800	17.78	.700	15.24	.600		015-91-1161	015-91-6164	015-91-1162	015-91-6165	015-91-1163	015-91-6166	015-91-1164	015-91-0167	015-91-1160									16		
18	22.86	.900	20.32	.800	17.78	.700		015-91-1181		015-91-1182		015-91-1183		015-91-1184	015-91-0187	015-91-1180									18		
20	25.40	1.000	22.86	.900	20.32	.800		015-91-1201		015-91-1202		015-91-1203		015-91-1204	015-91-0207	015-91-1200									20		
22	27.94	1.100	25.40	1.000	22.86	.900		015-91-1221		015-91-1222		015-91-1223		015-91-1224	015-91-0227	015-91-1220									22		
24	30.48	1.200	27.94	1.100	25.40	1.000		015-91-1241	71308-6901	015-91-1242		015-91-1243		015-91-1244	015-91-0247	015-91-1240									24		
26	33.02	1.300	30.48	1.200	27.94	1.100		015-91-1261		015-91-1262		015-91-1263		015-91-1264	015-91-0267	015-91-1260									26		
28	35.56	1.400	33.02	1.300	30.48	1.200		015-91-1281		015-91-1282		015-91-1283		015-91-1284	015-91-0287	015-91-1280									28		
30	38.10	1.500	35.56	1.400	33.02	1.300		015-91-1301		015-91-1302		015-91-1303		015-91-1304	015-91-0307	015-91-1300									30		
32	40.64	1.600	38.10	1.500	35.56	1.400		015-91-1321		015-91-1322		015-91-1323		015-91-1324	015-91-0327	015-91-1320									32		
34	43.18	1.700	40.64	1.600	38.10	1.500		015-91-1341		015-91-1342		015-91-1343		015-91-1344	015-91-0347	015-91-1340									34		
36	45.72	1.800	43.18	1.700	40.64	1.600		015-91-1361		015-91-1362		015-91-1363		015-91-1364	015-91-0367	015-91-1360									36		
38	48.26	1.900	45.72	1.800	43.18	1.700		015-91-1381		015-91-1382		015-91-1383		015-91-1384	015-91-0387	015-91-1380									38		
40	50.80	2.000	48.26	1.900	45.72	1.800		015-91-1401		015-91-1402		015-91-1403		015-91-1404	015-91-0407	015-91-1400									40		
42	53.34	2.100	50.80	2.000	48.26	1.900		015-91-1421		015-91-1422		015-91-1423		015-91-1424	015-91-0427	015-91-1420									42		
44	55.88	2.200	53.34	2.100	50.80	2.000		015-91-1441		015-91-1442		015-91-1443		015-91-1444	015-91-0447	015-91-1440									44		
46	58.42	2.300	55.88	2.200	53.34	2.100		015-91-1461		015-91-1462		015-91-1463		015-91-1464	015-91-0467	015-91-1460									46		
48	60.96	2.400	58.42	2.300	55.88	2.200		015-91-1481		015-91-1482		015-91-1483		015-91-1484	015-91-0487	015-91-1480									48		
50	63.50	2.500	60.96	2.400	58.42	2.300		015-91-1501	015-91-6504	015-91-1502	015-91-6505	015-91-1503	015-91-6506	015-91-1504	015-91-0507	015-91-1500									50		
52	66.04	2.600	63.50	2.500	60.96	2.400		015-91-1521		015-91-1522		015-91-1523	71308-5203	015-91-1524	015-91-0527	015-91-1520									52		
54	68.58	2.700	66.04	2.600	63.50	2.500		015-91-1541		015-91-1542		015-91-1543		015-91-1544	015-91-0547	015-91-1540									54		
56	71.12	2.800	68.58	2.700	66.04	2.600		015-91-1561		015-91-1562		015-91-1563		015-91-1564	015-91-0567	015-91-1560									56		
58	73.66	2.900	71.12	2.800	68.58	2.700		015-91-1581		015-91-1582		015-91-1583		015-91-1584	015-91-0587	015-91-1580									58		
60	76.20	3.000	73.66	2.900	71.12	2.800		015-91-1601		015-91-1602		015-91-1603		015-91-1604	015-91-0607	015-91-1600									60		
62	78.74	3.100	76.20	3.000	73.66	2.900		015-91-1621		015-91-1622		015-91-1623		015-91-1624	015-91-0627	015-91-1620									62		
64	81.28	3.200	78.74	3.100	76.20	3.000		015-91-1641		015-91-1642		015-91-1643		015-91-1644	015-91-0647	015-91-1640									64		
66	83.82	3.300	81.28	3.200	78.74	3.100		015-91-1661		015-91-1662		015-91-1663		015-91-1664	015-91-0667	015-91-1660									66		
68	86.36	3.400	83.82	3.300	81.28	3.200		015-91-1681		015-91-1682		015-91-1683		015-91-1684	015-91-0687	015-91-1680									68		
70	88.90	3.500	86.36	3.400	83.82	3.300		015-91-1701		015-91-1702		015-91-1703		015-91-1704	015-91-0707	015-91-1700									70		
72	91.44	3.600	88.90	3.500	86.36	3.400		015-91-1721		015-91-1722		015-91-1723		015-91-1724	015-91-0727	015-91-1720									72		
74	93.98	3.700	91.44	3.600	88.90	3.500		015-91-1741		015-91-1742		015-91-1743		015-91-1744	015-91-0747	015-91-1740									74		
76	96.52	3.800	93.98	3.700	91.44	3.600		015-91-1761		015-91-1762		015-91-1763		015-91-1764	015-91-0767	015-91-1760									76		
78	99.06	3.900	96.52	3.800	93.98	3.700		015-91-1781		015-91-1782		015-91-1783		015-91-1784	015-91-0787	015-91-1780									78		
80	101.60	4.000	99.06	3.900	96.52	3.800		015-91-1801		015-91-1802		015-91-1803		015-91-1804	015-91-0807	015-91-1800									80		
82	104.14	4.100	101.60	4.000	99.06	3.900		71308-4082		71308-4182		71308-4282		71308-5082	71308-5182	71308-5282									82		
84	106.68	4.200	104.14	4.100	101.60	4.000		71308-4084		71308-4184		71308-4284		71308-5084	71308-5184	71308-5284									84		
86	109.22	4.300	106.68	4.200	104.14	4.100		71308-4086		71308-4186		71308-4286		71308-5086	71308-5186	71308-5286									86		
88	111.76	4.400	109.22	4.300	10																						

[illegible]

		13		12		11		10		9		8		7		6		5		4		3		2		1			
J		PACKAGING SEE NOTE 4, SHT 1		4-6 CKT		BULK		TAPE-N-REEL W/VAC CAPS		N/A		4-8 CKT		TAPE-N-REEL W/VAC CAPS		BULK		BULK		LONG PEG VERSION (.130")		SHORT PEG VERSION (.055")		BULK		TAPE-N-REEL W/ VAC CAPS			
						TUBES		TAPE-N-REEL W/VAC CAPS		TUBES W/ VAC CAPS				10-100 CKT		TAPE-N-REEL W/VAC CAPS		TUBES		TUBES		TUBES				TUBES			
				8-100 CKT																									
				DIM. M±0.25 MM				6.10 (.240)								8.13(.320)		13.59(.535)		6.10(.240)		8.13(.320)		6.10 (.240)					
				PLATING				59 TIN								59 TIN		59 TIN		59 TIN		59 TIN		59 TIN					
DIM. H				2.54(.100)										4.57(.180)		4.57(.180)		2.54(.100)		4.57(.180)		2.54(.100)							
I		CKTS		DIM. A		DIM. B		DIM. C		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		CKTS	
				MM IN		MM IN		MM IN																					
H		04		5.08 .200		2.54 .100		---		---		71308-5404		71308-5504		N/A				71308-6404		71308-6504		71308-6604				04	
		06		7.62 .300		5.08 .200		2.54 .100		71308-5406		71308-5506		N/A						71308-6406		71308-6506		71308-6606		71308-6706		71308-6806	
		08		10.16 .400		7.62 .300		5.08 .200		71308-5408		71308-5508		71308-5608						71308-6408		71308-6508		71308-6608		71308-6708		71308-6808	
		10		12.70 .500		10.16 .400		7.62 .300		71308-5410		71308-5510		71308-5610				71308-5810		71308-5910		71308-6410		71308-6510		71308-6610		71308-6810	
		12		15.24 .600		12.70 .500		10.16 .400		71308-5412		71308-5512		71308-5612								71308-6412				71308-6612			
		14		17.78 .700		15.24 .600		12.70 .500		71308-5414		71308-5514		71308-5614								71308-6414		71308-6514		71308-6614			
		16		20.32 .800		17.78 .700		15.24 .600		71308-5416		71308-5516		71308-5616				71308-5816				71308-6416		71308-6516		71308-6616			
		18		22.86 .900		20.32 .800		17.78 .700		71308-5418				71308-5618								71308-6418				71308-6618			
		20		25.40 1.000		22.86 .900		20.32 .800		71308-5420		71308-5520		71308-5620								71308-6420				71308-6620			
		22		27.94 1.100		25.40 1.000		22.86 .900		71308-5422				71308-5622								71308-6422				71308-6622			
G		24		30.48 1.200		27.94 1.100		25.40 1.000		71308-5424				71308-5624		71308-5724		71308-5824		71308-6424				71308-6624					
		26		33.02 1.300		30.48 1.200		27.94 1.100		71308-5426				71308-5626						71308-6426				71308-6626		71308-6726			
		28		35.56 1.400		33.02 1.300		30.48 1.200		71308-5428				71308-5628						71308-6428				71308-6628					
		30		38.10 1.500		35.56 1.400		33.02 1.300		71308-5430				71308-5630						71308-									