


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



CURL SLOTS IN P/N
DV10-250-2K ONLY

CERTIFIED
LR31212

LISTED
20H3
E78522

* NOT UL LISTED

NOTES:

1. UL LISTED AND CSA CERTIFIED FOR:
A. 600V MAX VOLTAGE RATING
B. 221°F (105°C) MAX TEMP RATING
C. STRANDED COPPER WIRE ONLY
D. 6-12 LBS INITIAL INSERTION/WITHDRAWAL FORCE
2. PACKAGE QTY: 2K=2000 PIECES, 3K=3000 PIECES
3. MATERIAL: CONTINUOUS MOLDED STRIP CARRIER
A. STAMPING-CDA 260 BRASS, TIN PLATED
B. HOUSING-PVC
4. DIMENSIONS IN BRACKETS ARE IN mm OR mm²
5. PART NUMBER DV10-250 IS CONSTRUCTED WITH BRASS SLEEVE IN WIRE CRIMP AREA
6. WIRE STRIP LENGTH 9/32 ^{+1/32}/₋₀
(11/32 ^{+1/32}/₋₀ FOR DV10-250-2K)

PART NUMBER	TAB SIZE	WIRE RANGE AWG	COLOR	MAX. INSUL.	DIMENSIONS in.			TOOL CHART-RECOMMENDED PRESSES: CP-851, CP-860, CP-861, CP-862 CA-800 & CA9 APPLICATOR DIES
					A ±.03 (.8)	B ±.01 (.3)	C ±.01 (.3)	
DV18-250B-3K	.250 X .032 (6.3 X 0.8)	22-18 (0.5-1.0)	RED	.15 (3.8)	.83 (21.1)	.29 (7.4)	.12 (3.0)	CD-800-1 CD9-1A
DV18-205B-3K	OR .205 X .032 .187 X .032	22-18 (0.5-1.0)	RED	.15 (3.8)	.77 (19.6)	.25 (6.4)	.12 (3.0)	
DV18-206B-3K	OR .205 X .020 .187 X .020	22-18 (0.5-1.0)	RED	.15 (3.8)	.77 (19.6)	.25 (6.4)	.11 (2.8)	
DV18-187B-3K	.187 X .032 (4.8 X 0.8)	22-18 (0.5-1.0)	RED	.15 (3.8)	.77 (19.6)	.23 (5.8)	.10 (2.5)	
DV18-188B-3K	.187 X .020 (4.8 X 0.5)	22-18 (0.5-1.0)	RED	.15 (3.8)	.77 (19.6)	.23 (5.8)	.09 (2.3)	
DV14-250B-3K	.250 X .032 (6.3 X 0.8)	16-14 (1.5-2.5)	BLUE	.17 (4.3)	.83 (21.1)	.29 (7.4)	.12 (3.0)	CD-800-2 CD9-2A
DV14-205B-3K	OR .205 X .032 .187 X .032	16-14 (1.5-2.5)	BLUE	.17 (4.3)	.77 (19.6)	.25 (6.4)	.12 (3.0)	
DV14-206B-3K	OR .205 X .020 .187 X .020	16-14 (1.5-2.5)	BLUE	.17 (4.3)	.77 (19.6)	.25 (6.4)	.11 (2.8)	
DV14-187B-3K	.187 X .032 (4.8 X 0.8)	16-14 (1.5-2.5)	BLUE	.17 (4.3)	.77 (19.6)	.23 (5.8)	.10 (2.5)	
DV14-188B-3K	.187 X .020 (4.8 X 0.5)	16-14 (1.5-2.5)	BLUE	.17 (4.3)	.77 (19.6)	.23 (5.8)	.09 (2.3)	
*DV10-250-2K	.250 X .032 (6.3 X 0.8)	12-10 (4.0-6.0)	YELLOW	.23 (5.8)	.95 (24.1)	.29 (7.4)	.12 (3.0)	CD-800-3 CD9-3B

07	5/04	JHNU		ADDED CURL SLOTS IN VIEW					
06	8/02	SABSKB		ADDED CP-862, CA9, CD9-1A, CD9-2A, & CD9-3B TO TOOL CHART. WIRE RANGE FOR DV18-250B-3K, DV18-205B-3K, DV18-206B-3K, DV18-187B-3K, & DV18-188B-3K WERE (.05-1.8), FOR DV10-250-2K WAS (2.5-6.0), & WASN'T CSA CERTIFIED	10347	LCA	TRO		
---	---	---	---		---	---	---		
05	1/01	KMD		CAD FILE SPEC. WAS N41169AA_PCD_04	08938				
04	6/97	JAMB		DV18/14-187/188B-3K HAS UL/CSA MAX. INSUL DIA. FOR DV18 PARTS, WAS .16 (4.1)	06013				
REV	DATE	BY	CHK	DESCRIPTION	ECN#	CUST	PM	DRAWN BY DSM	CHK'D LA
								SCALE NONE	DRAWING NO./CAD FILENAME A41169

PANDUIT CORP.

A41169_07

TINLEY PARK, ILLINOIS

DISCO-FEMALE DISCONNECTS, VINYL INSULATED
.250 X .032, .205 X .032/.020, .187 X .032/.020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[DV14-250B-3K](#) [DV18-205B-3K](#)