

Datasheet

Item No. 80.020.2004.0

Solid state relay WRS-SSDC-60V5A

WRS-solid-state-relays DC, solid state relay not plugable, with LED, open module housing WEB 1002. 80x12,5mm (HxW), control voltage: 24V DC, output: 60 V DC/5A, please note, that the negative pole of the control side can be bridged to the neighboring module. These jumpers have to be ordered separately if required.



Item No.	80.020.2004.0
EAN	4015573440845
order unit	10 Piece(s)

Approvals



Technical data

General

Modular version	No
-----------------	----

Technical data

Connection type	Screw connection
Min. connection voltage	3 V
Max. connection voltage	60 V
Rated operating current DC	5 A
Min. control voltage	24 V

Dimensions

Depth	59 mm
Width	12.5 mm
Height	80 mm