

HS16-12



## ***Shrink-Kon®***

HS Series Heavy-Wall Heat-Shrinkable  
Tubing — Black

### General

|                     |                                   |
|---------------------|-----------------------------------|
| T&B Sales Drawings: | WSD-000473                        |
| Type:               | Heavy-Wall Heat-Shrinkable Tubing |
| Shrink Ratio:       | 3:1                               |
| Color:              | Black                             |
| T&B UPC:            | 78621089833                       |
| T&B Status:         | M                                 |
| Material:           | Thermoplastic adhesive liner      |

### Dimension Information

|                                   |                |
|-----------------------------------|----------------|
| Cable Range:                      | #14 to #10 AWG |
| Max. Recovered I.D. (in):         | 0.12           |
| Max. Recovered I.D. (mm):         | 3.00           |
| Min. Expanded I.D. (in):          | 0.35           |
| Min. Expanded I.D. (mm):          | 8.90           |
| Nom. Recovered Wall (in):         | 0.07           |
| Nom. Recovered Wall (mm):         | 1.80           |
| Std. Length (in.):                | 3              |
| Continuous Operating Temperature: | -55°C to 110°C |
| Shrink Temperature:               | 120°C          |