


3. THIS PART CODED "NCA". API TECHNOLOGIES DOES NOT HAVE CHANGE AUTHORITY. CUSTOMER APPROVAL REQUIRED BEFORE PRODUCT/PROCESS CHANGES CAN BE MADE.



LEAD FINISH: SOLDER	
BUSHING FINISH: SOLDER COATED	
CAPACITANCE	3000pF +100/-0%
TEMP. RANGE	-55°C TO 125°C
CURRENT	15 AMP MAX.
WORKING VOLTAGE	85°C 85 VAC MAX. 125°C 125 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
10	10
30	--
100	30
500	55
1-10 GHz	65

NOTE: PACKAGE TO BE MARKED SAME AS THE BAG.

	46	45	44	43	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 FAIRVIEW PENNSYLVANIA	
	CN 68508-ENG	CN 23396-CPD	CN 211855	CN 184950	CHANGE NOTICE	Fractions $\pm 1/64$	Dwn. KAUFFMAN	Description Pi
						Dec. .xx $\pm$	Date 4-23-13	RESIN SEAL FILTER
						Dec. .xxx $\pm$.005	Engr. M.McALEVY	51-744-003
						Angles $\pm 0^{\circ} 30'$	Scale NONE	
						CODE IDENT. NO. DLSP2		