



HAHN - Elektrobau GmbH & Co. KG

Bellersheimerstraße 45
35410 Hungen
Germany

phone: +49 (0) 6402/808-0
fax: +49 (0) 6402/808-60
email: info@hahn-trafo.de

Data sheet: BV EI 306 2073

Size 6 a: height 33.8 mm

3,2 VA

ta 40/F

BV EI 306 ...

Several hundreds of types provide high electrical safety and long service-life for printed circuit boards, household appliances, leisure electronics, heating and control technology as well as in assembly techniques. Transformers for special requirements with lower open -circuit (no-load) loss capacity are also available in the range.

absolutely short-circuit-proof

minimal size

test certifications to ENEC 10, VDE, UL- and CSA-regulations

vacuum encapsulated, bobbin with dual chamber windings

temperature class ta 40°C/F and ta 70°C/F

high electrical safety and long service -life properties

individually tested with certificate

excellent temperature fluctuation resistance properties

self-extinguishing cast housing and sealing material



Article no. BV	Output ta 40°C/F	prim.V	Connecting pins	Operating point sec. ± 5%	Connecting pins	No-load voltage V ± 5%
BV EI 306 2073	3,2	230	1-5	15 V 213 mA	7-9	26,7

Dimensions with no indication of tolerances ± 0,3mm.