

Item # ATV312HU22N4, Variable Speed Drive



Variable Speed Drive  
Variable Speed Drive

SPECIFICATIONS

|                      |                 |
|----------------------|-----------------|
| Family               | Altivar 312     |
| Product Line         | AC Drives       |
| Output Ampere Rating | 5.5             |
| Application          | Constant Torque |
| Enclosure Rating     | IP20            |
| Frame Size           | 7               |
| HP Rating            | 3               |
| kW Rating            | 2.2             |
| Voltage Rating       | 400/480VAC      |
| Input Phase          | 3 Phase         |
| Output Phase         | 3 Phase         |
| Control Voltage      | 24Vdc           |
| Logic Input          | 6               |
| Analog Input         | 3               |

|                     |                              |
|---------------------|------------------------------|
| Analog Output       | 1                            |
| Logic/Relay Outputs | 1 Form C, 1 NO               |
| Weight [lb]         | 5.18                         |
| Weight [kg]         | 2.35                         |
| UL File No.         | E116875                      |
| CSA File            | 1464725                      |
| Other               | CE, GOST, RoHS, NOM, EMITECH |
| Communication       | Modbus and CANopen           |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ATV312HU22N4](#)