

Switchcraft®

3.5 mm MOLDED CABLES

NEW
PRODUCT
BULLETIN

511



35HRXXX35



36HRXXX36



35HRXXX84

FEATURES AND BENEFITS

- Choose plug-to-plug or plug-to-stripped and tinned leads
- 3.5 mm plugs available as straight or right-angle
- Available in mono and stereo
- NOM.29 GA jacketed conductors (red and white) with copper spiral shield
- Cable O.D. 3.0 mm nom./ .118" nom.
- Black cable

SPECIFICATIONS

PLUGS

Tip, Ring and Sleeve: Brass with nickel-plate

Flex Life: 5000 cycles minimum

Plug Insulator: ACETAL

PART NUMBERING SYSTEM



32 - Mono
33 - RA
Mono
35 - Stereo
36 - RA
Stereo



H -
Black



R - 3.0 mm nom.
2-conductor wire
with spiral cop-
per shield



Length
(feet)
036 (3)
072 (6)
144 (12)



32 - Mono
33 - RA Mono
35 - Stereo
36 - RA
Stereo
84 - Stripped
and
tinned

ORDERING INFORMATION

1. Order by part number.
2. Contact Switchcraft for custom requirements.

FAX

To: _____

From: _____

Date: _____

Switchcraft®