

Caps for Holder FEU (Grip)



250 VAC · 20 A (UL/CSA)

**Standards**

- IEC 60127-6
- UL 4248-1 / UL 512
- CSA C22.2 no. 39

Approvals

- VDE Certificate Number: 134125
- UL File Number: E39328

References

Fits to type:

Weblinks



General Product Information, Approvals, RoHS, CHINA-RoHS, e-Store, SCHURTER-Stock-Check, Distributor-Stock-Check

Technical Data

Fuse-Link	5 x 20 or 6.3 x 32 mm
Rated Voltage	250 VAC
Rated Current	10 A (VDE), 20 A (UL/CSA)
Degree of Protection	IP 40
Admissible Ambient Air Temp.	-40 °C to 85 °C
Material: Cap	Thermoset
Storage Conditions	0 °C to 60 °C, max. 70% r.h.

Abmessungen

29.5 mm

**Variants [nicht konfiguriert]**

Order	Type	Holder	Clip	Strip	Cap	Fuse-	Panel	Rated	Termi-	Termi-	Pin di-	Termi-	Moun-	Wire

Packaging Unit

Plastic Bag (100 pcs.)