

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1302430004](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Haztex Hazardous and Wet Location Work Light 55W Twin Fluorescent without Cable



Series image - Reference only

Documents:
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Portable Lighting
Series [130243](#)
Comments Class 1, Division 2, Groups B, C, and D, Class 1, Division 2, Groups B, C, and D
NEMA Configuration N/A
NEMA Rating NEMA 3R
Outlet None
Overview [Wide-Area Lighting Products](#)
Product Name Haztex
Type Wide Area Lamps
UPC 78172506166

Physical
Cord Length - Primary N/A
Cord Length - Secondary N/A
Depth 176.90m (6.960")
Duty Hazardous
Guard Included No
Guard Type N/A
Height 166.50mm (6.555")
Length 706.37mm (27.810")
Material - Globe Clear Polycarbonate
Material - Guard Silicone Rubber
Mounting Style Variable
Packaging Type Carton
Socket Construction N/A

Electrical
Bulb Type Fluorescent
Lamp Type PL-L 55/841/B
Lamp Wattage - Maximum 55W
Lumens 4800
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info
Engineering Number 1075HZ2N000

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130243](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION