


Dimensions: mm (In.)



Mount Hole

Circuit Structure

Thickness	X	Y
0.75...1.25	30.2 - 0.1	22.2 + 0.1
1.25...2	30.4 - 0.1	22.2 + 0.1
2...3	30.8 - 0.1	22.2 + 0.1

Mouser Stock No.	Button Color
103-7078-EV	Black
103-7080-EV	Green (Illuminated)

Electrical Specifications:

- Rating: 16A / 125VAC, 10A / 250 VAC
- Contact Resistance: 50m Ω max.
- Insulation Resistance: 500 VDC 100M Ω min.
- Dielectric Strength: 1500 VAC for 1 minute

Mechanical Specifications:

- Operating Temperature: -20°C ~ 85°C
- Circuit: 4P DPST On-Off
- Neon Lamp (103-7080-EV): 110VAC

Note:

- RoHS Compliant

Rocker Switches
103-7078-EV, 103-7080-EV

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[103-7078-EV](#) [103-7080-EV](#)