

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


130110-0051

Status:

Active

Description:

Pro-Yellow® 250W Metal Halide High Bay Light with Lamp Molded 18/3 SJTW 1.83m Pulse Start



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Portable Lighting
Series	130110
NEMA Configuration	NEMA 5-15
NEMA Rating	Rain Tight
Outlet	None
Product Name	Pro-Yellow®
Type	Wide Area Lamps
Woodhead	Yes
Physical	
Cord Length - Primary	0.91m
Cord Length - Secondary	N/A
Depth	N/A
Duty	General
Guard Included	No
Guard Type	N/A
Height	463.55mm
Length	N/A
Material - Guard	#10 Gauge Zinc-plated Steel
Mounting Style	Hook
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Metal Halide - Pulse Start
Cord Type - Primary	16/3 SOOW
Lamp Type	BT37/ED-37 Type O
Lamp Wattage - Maximum	250W
Lumens	14000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Old Part Number	8573-MH-PS

EU RoHS

China RoHS

RoHS Compliance

Not Required

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130110Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION